

VPU series
VPU I 4 400V/25KA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

Type I/II lightning arrester for use in 400/690 V mains systems

- Can also be used as Type II surge protection
- With remote monitoring function, one changeover contact
- Tested according to IEC 61643-11 for Type I and II surge protection
- Pluggable arrester

General ordering data

Type	VPU I 4 400V/25KA
Order No.	1438010000
Version	Surge voltage arrester, Low voltage, without telecomm. contact, TN-C-S, TN-S
GTIN (EAN)	4050118243703
Qty.	1 pc(s).

VPU series VPU I 4 400V/25KA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	142.4 mm	Width (inches)	5.606 inch
Height	106 mm	Height (inches)	4.173 inch
Depth	69 mm	Depth (inches)	2.717 inch
Mounting dimension - height	75 mm	Net weight	1,530 g

Temperatures

Humidity	5 - 95% rel. humidity	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	80 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...80 °C		

General data

Colour	black, orange	Design	Installation housing; 8 TE, Insta IP 20
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
Rail	TS 35	Segment	Power distribution
UL 94 flammability rating	V-0	Version	without telecomm. contact

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	IV
--------------------	---	------------------------	----

Rated data IEC / EN

Discharge current $I_{\max}$ (8/20 μ s) wire-PE	100 kA	Discharge current I_n (8/20 μ s) wire-PE	25 kA
Follow-on current extinguishing capability I_{fi}	Not available due for technical reasons	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	250 A gL (if back up fuse > 250 A)
Leakage current at U_n	100 μ A	Lightning test current I_{imp} (10/350 μ s) (L-PE)	25 kA
Low voltage network	TN-C-S, TN-S	Max. continuous voltage, U_c (AC)	400 V
No. of poles	8	Protection level U_p at I_N (L/N-PE)	≤ 1.9 kV
Rated load current I_L	100 A	Rated voltage (AC)	400 V
Requirements category acc. to IEC 61643-11	Type I, Type II	Requirements class, acc. to EN 61643-11	T1, T2
Response time	≤ 25 ns	Short-circuit current rating I_{SCCR}	25 kA
Signalling contact	No	Standards	IEC61643-11, EN61643-11
Temporary surge voltage (over-voltage) - TOV	620 V	Voltage type	AC

VPU series
VPU I 4 400V/25KA
Weidmüller Interface GmbH & Co. KG

 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Connection data

Type of connection	Screw connection	Stripping length, rated connection	15 mm
Tightening torque, min.	2 Nm	Tightening torque, max.	3 Nm
Clamping range, rated connection	16 mm ²	Clamping range, min.	4 mm ²
Clamping range, max.	35 mm ²	Wire cross-section, solid, min.	2.5 mm ²
Wire cross-section, solid, max.	16 mm ²	Wire connection cross-section, finely stranded, min.	2.5 mm ²
Wire connection cross section, finely stranded, max.	25 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), min.	2.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	50 mm ²	Connection cross-section, stranded, min.	2.5 mm ²
Connection cross-section, stranded, max.	50 mm ²		

Classifications

ETIM 3.0	EC000381	ETIM 5.0	EC000510
ETIM 6.0	EC000941	UNSPSC	30-21-19-22
eClass 5.1	27-14-02-01	eClass 6.2	27-13-08-02
eClass 7.1	27-14-02-01	eClass 8.1	27-14-02-01
eClass 9.0	27-13-08-05	eClass 9.1	27-13-08-05

Approvals

Approvals



ROHS

Conform

Downloads


Approval/Certificate/Document of Conformity	CE PAPER Declaration of Conformity
Brochure/Catalogue	CAT 4.4 ELECTR 16/17 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
User Documentation	Instruction sheet

VPU series VPU I 4 400V/25KA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Electric symbol



Schematic circuit diagram