

W-Series
WSI 25/3 10X38/LED

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WSI 25/3 10X38/LED
Order No.	1444240000
Version	W-Series, Fuse terminal, Rated cross-section: 25 mm ² , Screw connection
GTIN (EAN)	4050118249552
Qty.	4 pc(s).

W-Series
WSI 25/3 10X38/LED

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	54 mm	Width (inches)	2.126 inch
Height	81 mm	Height (inches)	3.189 inch
Depth	58 mm	Depth (inches)	2.283 inch
Net weight	104 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	PA 66/6	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Number of potentials	1	Number of levels	1
No. of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35	N-function	No
PE function	No	PEN function	No

Additional technical data

Type of mounting	Snap-on
------------------	---------

Conductors for clamping (rated connection)

Number of connections	2	Stripping length	11 mm
Type of connection	Screw connection		

Fuse terminals

Cartridge fuse	max. 3W for gG/gL max. 1.2W for aM	Permitted power loss for fuse with semiconductor protection
Power loss, 1-pole ; 2-pole ; 3-pole		

Rating data

Rated cross-section	25 mm ²	Rated voltage	690 V
Rated voltage to adjoining terminal	690 V	Rated current	32 A
Current at maximum wires	32 A	Volume resistance according to IEC 60947-7-x	0.96 mΩ
Rated impulse withstand voltage	6 kV	Pollution severity	3

Classifications

ETIM 6.0	EC000899	eClass 6.2	27-14-11-16
eClass 8.1	27-14-11-16	eClass 9.0	27-14-11-16
eClass 9.1	27-14-11-16		

W-Series WSI 25/3 10X38/LED

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of conformity
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP