

**cable lug, terminal end  
VSTN/120**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

Type	VSTN/120
Order No.	<a href="#">1493110000</a>
Version	cable lug, terminal end, 120 mm <sup>2</sup> , 120 mm <sup>2</sup>
GTIN (EAN)	4050118302813
Qty.	50 pc(s).

**cable lug, terminal end  
VSTN/120**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Weight	8.67 g	Net weight	86.7 g
--------	--------	------------	--------

**Connectors**

Conductor cross-section	120 mm <sup>2</sup>	Conductor cross-section, max.	120 mm <sup>2</sup>
Connection length (l)	52 mm	Inside diameter of shaft (d1)	16.7 mm
Insulation	not available	Outside diameter of shaft (d3)	22.7 mm

**Classifications**

ETIM 3.0	EC001509	ETIM 4.0	EC001509
ETIM 5.0	EC001052	ETIM 6.0	EC001059
eClass 6.2	27-40-02-04	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-04	eClass 9.0	27-40-02-12
eClass 9.1	27-40-02-12		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
--------------------	--------------------------------------

**Data sheet**

**cable lug, terminal end  
VSTN/120**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

