HSS-HF 1.2-2.4 EL Y30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The continuous shrink sleeves of the MultiMark series are printed in seconds using our thermo-transfer printers. The length of the marker can be individually adjusted to suit the number of characters or available space. The required length is pre-perforated precisely using a special blade. With their oval shape the markers can be opened easily, applied quickly and shrunk precisely to fit the conductor. An external reel holder (1302920000) has to be used for reels above 30 m printing material.

General ordering data

Type	HSS-HF 1.2-2.4 EL Y30M
Order No.	1513140000
Version	Conductor and cable markers, 1.2 - 2.4 mm, x 4.2 mm, yellow
GTIN (EAN)	4050118320794
Qty.	1 pc(s).
compatible printer	2430920000 2448870000 1140490000

HSS-HF 1.2-2.4 EL Y30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	30,000 mm	Length (inches)	1,181.1 inch
Width	4.2 mm	Width (inches)	0.165 inch
Depth	0.5 mm	Depth (inches)	0.02 inch
Net weight	158 g		

General data

Colour	yellow	Halogen	No
Length	30,000 mm	Material	Polyolefine
Number per roll	1	Operating temperature range	-55…105 °C
Width	4.2 mm		

Conductor and cable markers

Conductor O.D.	1.2 - 2.4 mm	Conductor O.D., max.	2.4 mm
Conductor O.D., min.	1.2 mm	Conductor cross-section, max.	0.5 mm²
Conductor cross-section, min.	0.25 mm²	Halogen	No
Rate of shrinkage	2:1	Recommended shrinking temperature	90 °C

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform

Downloads

Approval/Certificate/Document of Conformity	NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN 45545-2 2013+A1 2015 BS EN ISO 4589-2 1999
Engineering Data	EPLAN, WSCAD

HSS-HF 1.2-2.4 EL Y30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

