W-Series
WEW 35/1 V0 GF SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image



Klippon® Connect with clamping yoke Technology
The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easer and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WEW 35/1 V0 GF SW
Order No.	1478990000
Version	W-Series, End bracket
GTIN (EAN)	4050118286892
Qty.	50 pc(s).

W-Series
WEW 35/1 V0 GF SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	12 mm	Width (inches)	0.472 inch
Height	56 mm	Height (inches)	2.205 inch
Depth	63 mm	Depth (inches)	2.48 inch
Net weight	37.82 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	130 °C

Material data

Material	Wemid	Colour	black
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals	Rail	TS 35

Additional technical data

Installation advice	Direct mounting	Interlock	for screw fixing
Type of fixing	when screwed in	Type of mounting	when screwed in
With snap-in pegs	No		

Conductors for clamping (rated connection)

Tightening torque, max.	2.4 Nm	Tightening torque, min.	2.4 Nm

Classifications

ETIM 5.0	EC002848	ETIM 6.0	EC001041
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14
eClass 8.1	27-14-11-35	eClass 9.0	27-14-11-35
eClass 9.1	27-14-11-35		

Approvals

Approvals	
ROHS	Conform

Downloads

Approval/Certificate/Document of Conformity	DNV GL certification
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP