
SAIE-M12BL-0.3VFM16-1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Type	SAIE-M12BL-0.3VFM16-1.5
Order No.	2530780000
Version	Built-in plugs, M12, Female socket, straight, M 16, No. of poles: 5
GTIN (EAN)	4050118540901
Qty.	1 pc(s).

SAIE-M12BL-0.3VFM16-1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	50 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

General data

Cable glands	M 16	Coding	L
Conductor O.D.	-	Connection thread	M12
Contact material	Cu	Contact surface	Gold-plated
Core cross-section	1.5 mm²	Housing main material	Zinc diecast
No. of poles	5	Plugging cycles	500
Protection degree	IP67, when screwed in	Rated current	16 A
Rated voltage	63 V	Strand / cable length	0.3 m
Temperature range of housing	-40 ... +85 ° C		

Classifications

ETIM 6.0	EC002638	eClass 6.2	27-26-07-02
eClass 9.0	27-44-03-09	eClass 9.1	27-44-03-09

Approvals


ROHS	Conform

SAIE-M12BL-0.3VFM16-1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing



Installation cut-out