

FAD BLK9 2XHE20 M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The front adapters for migration are connected to the old PLC and, by means of a new pre-assembled cable, to the new one. Some adapters have 2 connectors for redundancy.

General ordering data

Type	FAD BLK9 2XHE20 M
Order No.	1985970000
GTIN (EAN)	4050118370898
Qty.	1 pc(s).

FAD BLK9 2XHE20 M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Length	218 mm	Length (inches)	8.583 inch
Width	53.6 mm	Width (inches)	2.11 inch
Height	36.4 mm	Height (inches)	1.433 inch
Net weight	210 g		

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-25 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-40 °C
Operating temperature	-25...50 °C	Storage temperature	-40...60 °C

Connection data

Connection (field side)	2 x Connector according IEC60603-13/DIN41651 20 p
-------------------------	---

Ratings data

Operating voltage	30 V AC / 60 V DC	Max. current per channel	1 A
Max. current per byte	2 A	Total operating current	6 A

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 250 V AC
Surge voltage category	III	Pollution severity level	2
Insulation test voltage	1.2 kVAC	Storage temperature, min.	-40 °C
Storage temperature, max.	60 °C		

Classifications

ETIM 5.0	EC002780	ETIM 6.0	EC002584
eClass 6.2	27-14-11-52	eClass 7.1	27-14-11-52
eClass 8.1	27-14-11-52	eClass 9.0	27-33-02-92
eClass 9.1	27-24-22-92		

Approvals

Approvals



ROHS

Conform

DownloadsEngineering Data [EPLAN](#)

FAD BLK9 2XHE20 M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

