

SAIB-VSA-3P/24/9/SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Customisable valve plugs are used frequently in special-purpose machine engineering. Such plugs are used to connect solenoid valves. The valve plugs are available in all standard design types. The range includes the design types A, B Industrial, B acc. to DIN, C Industrial and C acc. to DIN. The valve plugs are available in 3 and 4-pole versions without cables. A flat gasket seal is included which, when screwed on, guarantees IP 65 protection.

General ordering data

Type	SAIB-VSA-3P/24/9/SD
Order No.	2451220000
Version	Valve plug-in connector, Socket, angled
GTIN (EAN)	4050118465426
Qty.	1 pc(s).

SAIB-VSA-3P/24/9/SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	26 g
------------	------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data customisable plug-in connectors

All valve plugs are fitted with protective circuits		Cable diameter, max.	
	Suppressor diode		7 mm
Cable diameter, min.	4.5 mm	Coding	Design A (18 mm)
Connection cross-section, max.	1.5 mm ²	Contact surface	CuSn
Housing main material	PA 6 GF	No. of poles	3
Plugging cycles	≤ 50	Pollution severity	3
Protection degree	IP65	Rated current	10 A
Rated voltage	24 V	Shield connection	No
Temperature range of housing	-30...+90 °C	Type of connection	Screw connection

Classifications

ETIM 6.0	EC002062	eClass 6.2	27-26-07-03
eClass 9.0	27-44-01-05	eClass 9.1	27-06-03-12

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL FIELDWIRING EN
--------------------	-----------------------------------