

HSS-HF 1.6-3.2 EL R30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The continuous shrink sleeves of the MultiMark series are printed in seconds using our thermo-transfer printers. The length of the marker can be individually adjusted to suit the number of characters or available space. The required length is pre-perforated precisely using a special blade. With their oval shape the markers can be opened easily, applied quickly and shrunk precisely to fit the conductor. An external reel holder (1302920000) has to be used for reels above 30 m printing material.

General ordering data

Type	HSS-HF 1.6-3.2 EL R30M
Order No.	1562750000
Version	Conductor and cable markers, 1.6 - 3.2 mm, x 5.6 mm, red
GTIN (EAN)	4050118367607
Qty.	1 pc(s).
compatible printer	2430920000 2448870000 1140490000

HSS-HF 1.6-3.2 EL R30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Length	30,000 mm	Length (inches)	1,181.1 inch
Width	5.6 mm	Width (inches)	0.22 inch
Depth	0.7 mm	Depth (inches)	0.028 inch
Net weight	227 g		

General data

Colour	red	Halogen	No
Length	30,000 mm	Material	Polyolefine
Number per roll	1	Operating temperature range	-55...105 °C
Width	5.6 mm		

Conductor and cable markers

Conductor O.D.	1.6 - 3.2 mm	Conductor O.D., max.	3.2 mm
Conductor O.D., min.	1.6 mm	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.5 mm ²	Halogen	No
Rate of shrinkage	2:1	Recommended shrinking temperature	90 °C

Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN 45545-2 2013+A1 2015 BS EN ISO 4589-2 1999
Engineering Data	EPLAN, WSCAD