

FAD
FAD S5115 SL24 M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The front adapters for migration are connected to the old PLC and, by means of a new pre-assembled cable, to the new one. Some adapters have 2 connectors for redundancy.

General ordering data

Type	FAD S5115 SL24 M
Order No.	1985980000
GTIN (EAN)	4050118371109
Qty.	1 pc(s).

FAD
FAD S5115 SL24 M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	280.45 mm	Length (inches)	11.041 inch
Width	46 mm	Width (inches)	1.811 inch
Height	24.7 mm	Height (inches)	0.972 inch
Net weight	203 g		

Temperatures

Operating temperature, max.	50 °C	Operating temperature, min.	-25 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-40 °C
Operating temperature	-25...50 °C	Storage temperature	-40...60 °C

Connection data

Connection (field side)	SL 5.08 mm
-------------------------	------------

Ratings data

Operating voltage	250 V AC	Max. current per channel	6 A
Total operating current	32 A		

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 250 V AC
Surge voltage category	II	Pollution severity level	2
Insulation test voltage	1.2 kVAC		

Classifications

ETIM 5.0	EC002780	ETIM 6.0	EC002584
eClass 6.2	27-14-11-52	eClass 7.1	27-14-11-52
eClass 8.1	27-14-11-52	eClass 9.0	27-33-02-92
eClass 9.1	27-24-22-92		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
------------------	-----------------------

FAD FAD S5115 SL24 M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

