

## SAIL-M12WM12G-S-5.0P

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

### General ordering data

Type	SAIL-M12WM12G-S-5.0P
Order No.	<a href="#">2050350500</a>
Version	Power cable, Connecting line, M12 / M12, Number of poles : 4 (3 + PE), 5 m, pin, angled - bush straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4050118441666
Qty.	1 pc(s).

**SAIL-M12WM12G-S-5.0P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 300 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Technical specifications for cable**

Number of poles	4 (3 + PE)	Core cross-section	1.5 mm <sup>2</sup>
Outside diameter	9.6 ± 0.3 mm	Cable length	5 m
Shielded	No	Insulation	PP
Colour coding	grey, black, brown, Green/ yellow	Sheath material	PUR
Sheathing colour	black	Halogen	No
Temperature range, moving	-40...80 °C	Temperature range, stationary	-50...80 °C
Outer cladding in accordance with UL AWM style	20234 (80 °C / 1000 V)	Suitable for cable carriers	Yes
Bending radius, min., stationary	5 x cable diameter	Bending radius, min., moving	10 x cable diameter
Acceleration	5 m/s <sup>2</sup>	Speed	5 m/s
Bending cycles	10 Mio	Resistant to welding beads	No
Hybrid cable	No	Irradiation crosslinked	No
Configurable cable length	No		

**General technical data**

Version	pin, angled - bush straight	Connection thread	M12 / M12
Housing main material	PUR	Coding	S
Protection degree	IP67, when screwed in	Contact surface	Gold-plated
LED	No	Rated voltage	600 V
Rated current	12 A	Insulation strength	10 <sup>8</sup> Ω
Temperature range of housing	-25...+85 °C	Plugging cycles	≥ 100
Pollution severity	3		

**Standards**

Connector standard IEC 61076-2-111

**Classifications**

ETIM 6.0	EC001855	eClass 6.2	27-26-07-02
eClass 9.0	27-06-03-11	eClass 9.1	27-06-03-11

**Approvals**

ROHS Conform

**Downloads**Brochure/Catalogue [FL FIELDWIRING EN](#)


**Data sheet**

**SAIL-M12WM12G-S-5.0P**


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Drawings**


**Dimensioned drawing**




**Dimensioned drawing**




**Pole scheme**



**Pole scheme**



**Wiring diagram**



**The ideal tool: Screwty® with torque function**

