

## SAIL-M12WM12W-T-1.5P

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

### General ordering data

Type	SAIL-M12WM12W-T-1.5P
Order No.	<a href="#">2050860150</a>
Version	Power cable, Connecting line, M12 / M12, Number of poles : 4, 1.5 m, pin, 90&deg; - socket 90&deg;, Shielded: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4050118442151
Qty.	1 pc(s).

## SAIL-M12WM12W-T-1.5P

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 100 g

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Technical specifications for cable

Number of poles	4	Core cross-section	1.5 mm <sup>2</sup>
Outside diameter	9.6 ± 0.3 mm	Cable length	1.5 m
Shielded	No	Insulation	PP
Colour coding	black, blue, white, brown	Sheath material	PUR
Sheathing colour	black	Halogen	No
Temperature range, moving	-40...90 °C	Temperature range, stationary	-50...90 °C
Outer cladding in accordance with UL AWM style	20234 (80 °C / 1000 V)	Suitable for cable carriers	Yes
Bending radius, min., stationary	5 x cable diameter	Bending radius, min., moving	10 x cable diameter
Acceleration	5 m/s <sup>2</sup>	Speed	5 m/s
Bending cycles	10 Mio	Resistant to welding beads	No
Hybrid cable	No	Irradiation crosslinked	No
Configurable cable length	No		

### General technical data

Version	pin, 90°; - socket 90°;	Connection thread	M12 / M12
Housing main material	PUR	Coding	T
Protection degree	IP67, when screwed in	Contact surface	Gold-plated
Rated voltage	63 V	Rated current	12 A
Insulation strength	10 <sup>8</sup> Ω	Temperature range of housing	-25...+85 °C
Plugging cycles	≥ 100	Pollution severity	3

### Standards

Connector standard IEC 61076-2-111

### Classifications

ETIM 6.0	EC001855	eClass 6.2	27-26-07-02
eClass 9.0	27-06-03-11	eClass 9.1	27-06-03-11

### Approvals

ROHS Conform

### Downloads

Brochure/Catalogue [FL FIELDWIRING EN](#)


**Data sheet**

**SAIL-M12WM12W-T-1.5P**


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Drawings**


**Dimensioned drawing**




**Dimensioned drawing**




**Pole scheme**



**Pole scheme**



**Wiring diagram**



**The ideal tool: Screwty® with torque function**

