

Features

- ANSI/AAMI/IEC/EN ES60601-1 (Edition 3.1)
- EMC: 60601-1-2 (Edition 4.0)
- IEC / EN 60950-1 Approval
- Means Of Protection: 2x MOPP
- Touch Current: < 100 μ A
- Regulated Output With Low Ripple Noise
- 1 Year Warranty



Marks / Approvals



ATM 120T-P
IEC 60320 C14



ATM 120T-A
IEC 60320 C8



Specifications

OUTPUT	MODEL	Voltage	Min. Load	Max. Load	Max. Power	Connector (mm)
	ATM 120T-P/A120	12 V	0.00 A	9.00 A	108 W	4-pin Mini-DIN
	ATM 120T-P/A150	15 V	0.00 A	8.00 A	120 W	4-pin Mini-DIN
	ATM 120T-P/A180	18 V	0.00 A	6.67 A	120 W	2.1 x 5.5 x 11
	ATM 120T-P/A190	19 V	0.00 A	6.32 A	120 W	2.1 x 5.5 x 11
	ATM 120T-P/A200	20 V	0.00 A	6.00 A	120 W	2.1 x 5.5 x 11
	ATM 120T-P/A240	24 V	0.00 A	5.00 A	120 W	2.1 x 5.5 x 11
	ATM 120T-P/A480	48 V	0.00 A	2.50 A	120 W	2.1 x 5.5 x 11
INPUT	Voltage	AC 100-240V				
	Frequency	50-60Hz				
	Current (rms max)	1.4A-0.5A				
	Protection	Internal Primary Current Fuse				
PROTECTION	Over Current	Yes				
	Overvoltage	Yes				
	Short Circuit	Yes				
	Over Temperature	Yes				
	Touch Current	< 100 μ A				
OTHERS	Topology	Switching Flyback				
	Dielectric Withstand	4000VAC Primary – Secondary				
	Efficiency	DoE Level VI; Energy Star; ErP Stage 2 Certified				
	Ripple	2% Vp-p Max. for Output Voltage @ Full Load				
	Transient Response	0.5 ms for 50% Load Change Typical				
Environment	Hold-Up Time	10 ms @ Full Load				
	Load Regulation	\pm 5% Typical				
	Temperature	Operating: 0°C – 40 °C (Storage: -20°C – 80°C)				
	Humidity	Operating: 20 – 80 % RH (Storage: 10 – 90 % RH)				
MTBF	300,000 Calculated Hours at 25°C, by Telcordia SR-332					
SAFETY	ANSI/AAMI/IEC/EN ES60601-1 (Edition 3.1)					
EMI	Compliance to EN 55011 Class B; EN 61000-3-2, -3					
EMS	Compliance to IEC/EN 60601-1-2					
Case Dimensions	165 mm x 66 mm x 39 mm					