

WIL-BM-SK-M12-3.0U**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The WIL-STANDARD: 24V DC LED lamp, only 8mm high, with very high light output (1315 lm) and long service life (greater than 10,000 h).

Extremely robust construction, solid encapsulation and metal housing - waterproof (IP67).

Its 6500K colour temperature (daylight) makes it suitable for a wide range of applications.

Very easy to connect thanks to M12 connector. Low current consumption means that a 24V, 0.5A DC power supply is sufficient for operation.

General ordering data

Type	WIL-BM-SK-M12-3.0U
Order No.	2537700000
GTIN (EAN)	4050118549140
Qty.	1 pc(s).

WIL-BM-SK-M12-3.0U**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	100 g
------------	-------

Temperatures

Operating temperature, max.	60 °C	Operating temperature, min.	-20 °C
Operating temperature	-20 - 60°C		

Cable technical specifications

Cable Material	PUR	Sheathing colour	black
Cable length	3 m		

Connection data

Connection thread	M12	Tightening torque	0.8 Nm
Wiring	PIN 4: + (black), PIN 3: - (blue)		

Electric data

Rated voltage (text)	24 V DC
----------------------	---------

Classifications

ETIM 6.0	EC002955	eClass 6.2	27-11-06-31
----------	----------	------------	-------------

Approvals

Approvals



ROHS	Conform
------	---------

www.weidmueller.com

Technical drawing of the Hager H3000-1000 power supply unit. The drawing shows the front and side views with dimensions in mm.

Dimensions:

- Top handle width: 75 mm
- Top handle height: 10 mm
- Front panel width: 100 mm
- Front panel height: 100 mm
- Side panel width: 100 mm
- Side panel height: 100 mm
- Unit width: 100 mm
- Unit height: 100 mm
- Unit depth: 100 mm

Labels:

- Hager H3000-1000
- CE
- Output
- Output

Legend:

- Schutzabstreifendkabel (Kupfer) (2 x 16 mm² max.)
- Schutzabstreifendkabel (Alu) (2 x 25 mm² max.)
- Kabelschutzhülse (außen diameter)

