

**WIL-TS-M12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The WIL door switch is pre-assembled with an M12 cable and an access line. This allows for a simple Plug and Produce feature with our WIL LED lamp series.

**General ordering data**

Type	WIL-TS-M12
Order No.	<a href="#">2537730000</a>
GTIN (EAN)	4050118549188
Qty.	1 pc(s).

**WIL-TS-M12**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight 120 g

**Temperatures**

Operating temperature, max. 60 °C      Operating temperature, min. -20 °C  
 Operating temperature -20 - 60°C

**Cable technical specifications**

Cable Material PUR      Sheathing colour black  
 Cable length 0.5 m

**Connection data**

Connection thread M12      Tightening torque 0.8 Nm  
 Wiring PIN 4: + (black), PIN 3: - (blue)

**Electric data**

Rated voltage (text) 24 V DC      Rated current 1.5 A

**General technical data**

Type of mounting Screw mounting      Drill hole spacing 21.5 mm  
 Protection degree IP67

**Classifications**

ETIM 6.0 EC002955      eClass 6.2 27-11-06-31

**Approvals**

Approvals




ROHS Conform

**WIL-TS-M12**


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Drawings**


**Dimensioned drawing**



**Dimensioned drawing**



**Dimensioned drawing**



**Dimensioned drawing**

