Constant Current LED Power Supply FCC linear series

SLT80-350IL-EU











Product description:

This type of power supply is an exclusively designed stabilized power supply for LED lamp. With constant current (CC)technology, it is suitable for constant current lamps connected in a series. According to the switches selection, the output current can change from 200mA to 350mA. The current step is 10mA.

The built-in protection circuit will shut down the power supply in case of such faults as: open circuit, short circuit, over load or over temperature. The power supply will restart automatically after fault correction.

Standards:

EN61347-1

EN61347-2-13

EN61547

EN55015

EN61000-3-2

EN61000-3-3

EN62384

EN62493

EN50172

Characteristics:

- Built-in power supply for constant current LED lamp
- Non-isolated Built-in design with functional ground, electric shock depend on the lamp
- Selectable output current according to the dipswitch from
- Push-in terminal block for quick connection with wire cross selection 0.75-1 mm²
- Open circuit, short circuit, over load and over temperature
- Auto restart after fault conditions removal
- Life time: 50,000h(ta=50°C)
- Warranty:5years




Last update:15,Nov,2018 Page: 1 of 5

Specifications:


Model		SLT80-350IL-EU															
	turn on time(S)	≤0.5															
Output	output current(mA)	200	210	220	230	240	250	260	270	280	290	300	310	320	330	340	350
	output current tolerance	+/-5%															
	output current regulation	±10%															
	ripple current(mA) ⁹	≤3%															
	working voltage range(V)	110-270 110-266 110-258 110-250 110-242 110-235 110-228															
	Max. output voltage(V)								420			'	1		ı		
	dimming interface	No															
	dimming range								n/a								
Input	rated supply voltage(Vac)							2	220-240)							
	voltage range(Vac)								198-264	1							
	line frequency(Hz)								50/60								
	input current(mA)	280	295	310	320	335	350	360	375	390	400	4	10	4	10	410	410
	efficiency ⁰	92.0%	92.0%	92.2%	92.5%	92.7%	92.8%	92.9%	93.1%	93.2%	93.4%	93	3.4%	93.	.3%	93.2%	93.1%
	power factor ²			-	-	-	-		0.90C			-					
	inrush current(lpk)							40)A/140	JS							
Protection	over voltage protection								n/a								
	short circuit protection								YES								
	over temperature protection		YES														
	automatic restart	YES															
	over load protection	YES															
	surge capacity	L-N: 1KV L,N-PE: 2KV															
Ambient and Life	Ta(℃)		-2050														
	Tc max. (˚C)	90															
	audible noise(dB)	20															
	Storage Temperature(℃)	-3080															
	ambient humidity range	5%85%RH, Not condensing															
	nominal life-time(hrs)	50'000@Tc															
Other	weight(g)								210								
	dimensions (L×W×H)(mm)	280x30x22															
	casing material	plastic															
	housing colour	grey															
	type of protection	IP20															
	protection class	Built-in															
Note	2.Tested at full load,230Vac 3.Output LF current ripple (4.All parameters NOT speci temperature. 5.The power supply is consi EMC performance will be o	1.Tolerance: includes set up tolerance, line regulation and load regulation. 2.Tested at full load,230Vac.Refer to "Power Factor" and "EFFICIENT" curve graphs. 3.Output LF current ripple (< 200 Hz) 4.All parameters NOT specially mentioned are measured at nominal voltage input, rated load and 25 of ambient temperature. 5.The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again.															



Dimensions(mm):





Wiring diagram:





Electrical curves:





note
For constant current power supply,"LOAD" means the percentage of the maximum rated output voltage.
For constant voltage power supply,"LOAD" means the percentage of the maximum rated output current.



Sales & Technical Support:

Self Electronics Co.,Ltd.

Add: No. 1345 Ju Xian Road, Ningbo Hi Tech Park, Ningbo,

Tel: 0086-574-28805765,28805658(For English Assistance)

0086-574-28805678 (For Chinese Assistance)

Fax: 0086-574-28805656

E-mail: sales@self-ecg.com

http://www.self-ecg.com

SELF ELECTRONICS GERMANY GMBH

Add:August-Horch-Str. 7,51149 Koeln

Tel: 0049 2203 18501-0

Fax: 0049 2203 18501-199

E-mail: saleseu@self-electronics.com

Self Electronics Co., Ltd., Shenzhen Office

Add: Room2007, Xinglang Xuan, Xinghe Mingju, Fuming

Road, Futian District, Shenzhen Tel: 0086-755-83558850, 83558851

Fax: 0086-755-83558840



^{*}Due to continuous improvements and innovations, specifications are subjected to change without notice.