


**OMNIMATE Signal - series B2C/S2C 3.50 - 2-row  
S2C-SMT 3.50/04/180LF 3.5SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

Similar to illustration

**High-temperature-resistant pin header.**

- touch-safe
- can be plugged into B2CF 3.50 PUSH IN female plug
- Plug-in direction is perpendicular or parallel to the circuit board (180° / 90°)
- Housing variants: closed (G) and with solder flange (LF)
- Box packaging (BX) or, anti-static, tape-on-reel (RL)
- Suitable for reflow and wave soldering applications
- Pin length of either 1.5 mm or 3.5 mm

**General ordering data**

| Type         | S2C-SMT 3.50/04/180LF 3.5SN BK BX                                                                                                                               |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Order No.    | <a href="#">1290220000</a>                                                                                                                                      |
| Version      | PCB plug-in connector, male header, Solder flange, THT/THR solder connection, 3.50 mm, No. of poles: 4, 180°, Solder pin length (l): 3.5 mm, tinned, black, Box |
| GTIN (EAN)   | 4050118083231                                                                                                                                                   |
| Qty.         | 132 pc(s).                                                                                                                                                      |
| Product data | IEC: 200 V / 13.4 A<br>UL: 150 V / 10 A                                                                                                                         |
| Packaging    | Box                                                                                                                                                             |

**OMNIMATE Signal - series B2C/S2C 3.50 - 2-row  
S2C-SMT 3.50/04/180LF 3.5SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**
**Dimensions and weights**

|                          |            |                 |            |
|--------------------------|------------|-----------------|------------|
| Width                    | 10.6 mm    | Width (inches)  | 0.417 inch |
| Height                   | 17.7 mm    | Height (inches) | 0.697 inch |
| Height of lowest version | 14.2 mm    | Depth           | 10.8 mm    |
| Depth (inches)           | 0.425 inch | Net weight      | 2.24 g     |

**System specifications**

|                                            |                                               |                                              |                        |
|--------------------------------------------|-----------------------------------------------|----------------------------------------------|------------------------|
| Product family                             | OMNIMATE Signal - series B2C/S2C 3.50 - 2-row | Type of connection                           | Board connection       |
| Mounting onto the PCB                      | THT/THR solder connection                     | Pitch in mm (P)                              | 3.5 mm                 |
| Pitch in inches (P)                        | 0.138 inch                                    | Outgoing elbow                               | 180°                   |
| No. of poles                               | 4                                             | Number of solder pins per pole               | 1                      |
| Solder pin length (l)                      | 3.5 mm                                        | Solder pin length tolerance                  | 0 / -0.3 mm            |
| Tolerance of solder pin position           | ± 0.1 mm                                      | Solder pin dimensions                        | d = 1.0 mm, Octagonal  |
| Solder pin dimensions = d tolerance        | +0,01 / -0,03 mm                              | Solder eyelet hole diameter (D)              | 1.3 mm                 |
| Solder eyelet hole diameter tolerance (D)+ | 0,1 mm                                        | Outside diameter of solder pad               | 2.1 mm                 |
| Template aperture diameter                 | 1.9 mm                                        | L1 in mm                                     | 3.5 mm                 |
| L1 in inches                               | 0.138 inch                                    | Number of rows                               | 1                      |
| Pin series quantity                        | 2                                             | Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch |
| Touch-safe protection acc. to DIN VDE 0470 | IP 20                                         | Can be coded                                 | Yes                    |
| Plugging cycles                            | 25                                            | Plugging force/pole, max.                    | 3.5 N                  |
| Pulling force/pole, max.                   | 2.5 N                                         |                                              |                        |

**Material data**

|                                       |                       |                                       |                       |
|---------------------------------------|-----------------------|---------------------------------------|-----------------------|
| Insulating material                   | LCP GF                | Colour                                | black                 |
| Colour chart (similar)                | RAL 9011              | Insulating material group             | IIIb                  |
| CTI                                   | ≥ 175                 | Insulation strength                   | ≥ 10 <sup>8</sup> Ω   |
| Moisture Level (MSL)                  | 1                     | UL 94 flammability rating             | V-0                   |
| GWIT                                  | 930 °C                | GWFI                                  | 960 °C                |
| Contact material                      | Copper alloy          | Contact surface                       | tinned                |
| Layer structure of solder connection  | 2-5 µm Sn / 1-3 µm Ni | Layer structure of plug contact       | 2-5 µm Sn / 1-3 µm Ni |
| Storage temperature, min.             | -25 °C                | Storage temperature, max.             | 55 °C                 |
| Max. relative humidity during storage | 80 %                  | Operating temperature, min.           | -50 °C                |
| Operating temperature, max.           | 120 °C                | Temperature range, installation, min. | -40 °C                |
| Temperature range, installation, max. | 120 °C                |                                       |                       |

**Rated data acc. to IEC**

|                                                                           |                        |                                                                       |                  |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. no. of poles (Tu=20°C)                            | 13.4 A           |
| Rated current, min. no. of poles (Tu=40°C)                                | 12 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 200 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 80 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 80 A |

**OMNIMATE Signal - series B2C/S2C 3.50 - 2-row  
S2C-SMT 3.50/04/180LF 3.5SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**
**Rated data acc. to CSA**

Institute (CSA)



Certificate No. (CSA)

200039-1121690

Rated voltage (Use group B / CSA) 150 V

Rated voltage (Use group C / CSA) 50 V

Rated voltage (Use group D / CSA) 150 V

Rated current (Use group B / CSA) 9.5 A

Rated current (Use group C / CSA) 9.5 A

Rated current (Use group D / CSA) 9.5 A

Reference to approval values

Specifications are  
maximum values, details -  
see approval certificate.

**Rated data acc. to UL 1059**

Institute (cURus)



Certificate No. (cURus)

E60693

Rated voltage (Use group B / UL 1059) 150 V

Rated voltage (Use group C / UL 1059) 50 V

Rated current (Use group B / UL 1059) 10 A

Rated current (Use group C / UL 1059) 10 A

Reference to approval values

Specifications are  
maximum values, details -  
see approval certificate.

**Packing**

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 35 mm  |
| VPE width | 135 mm | VPE height | 350 mm |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 4.0   | EC002637    | ETIM 5.0   | EC002637    |
| ETIM 6.0   | EC002637    | eClass 6.2 | 27-26-07-04 |
| eClass 7.1 | 27-44-04-02 | eClass 8.1 | 27-44-04-02 |
| eClass 9.0 | 27-44-04-02 | eClass 9.1 | 27-44-04-02 |

**Notes**

Notes

- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Spacing between rows: see hole layout
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

# OMNIMATE Signal - series B2C/S2C 3.50 - 2-row S2C-SMT 3.50/04/180LF 3.5SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS

Conform

### Downloads

Approval/Certificate/Document of  
Conformity
[Declaration of the Manufacturer](#)

Brochure/Catalogue

[FL DRIVES EN](#)  
[MB SMT EN](#)  
[FL DRIVES DE](#)  
[MB DEVICE MANUF. EN](#)  
[CAT 2 PORTFOLIOGUIDE EN](#)  
[FL BUILDING SAFETY EN](#)  
[FL APPL LED LIGHTING EN](#)  
[FL INDUSTR.CONTROLS EN](#)  
[FL MACHINE SAFETY EN](#)  
[FL HEATING ELECTR EN](#)  
[FL APPL INVERTER EN](#)  
[FL\\_BASE\\_STATION\\_EN](#)  
[FL ELEVATOR EN](#)  
[FL POWER SUPPLY EN](#)  
[FL 72H SAMPLE SER EN](#)  
[PO OMNIMATE EN](#)

Engineering Data

[EPLAN, WSCAD](#)

Engineering Data

[STEP](#)

SMT white paper


[Download Whitepaper](#)

## OMNIMATE Signal - series B2C/S2C 3.50 - 2-row S2C-SMT 3.50/04/180LF 3.5SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Dimensional drawing



The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Weidmüller exclusively reserves the right to file for patents, utility models or designs.

© Weidmüller Interface GmbH & Co. KG

Dimensions without tolerances are no check dimensions


The English version is binding



SHOWN: S2C-SMT 3.50/08/180G 3.5



SHOWN: S2C-SMT 3.50/08/180LF 3.5



P = 3.50 RASTER PITCH


D\* = Ø 1.3 +0.1 / -0.051"

d = 0.8x0.8 / 0.031"x0.031"


\* from n (no of poles) 26  
D = 1.4mm +0.1

|                          |      |        |
|--------------------------|------|--------|
| S2C-SMT 3.50...180LF 3.5 | 3.5  | 0.138  |
| S2C-SMT 3.50...180LF 1.5 | 1.5  | 0.059  |
| S2C-SMT 3.50...180G 3.5  | 3.5  | 0.138  |
| S2C-SMT 3.50...180G 1.5  | 1.5  | 0.059  |
| TYP PART NAME            | [mm] | [inch] |


M 1/1  
S2C-SMT 3.50/08/180G 1.5




M 1/1  
S2C-SMT 3.50/08/180G 3.5



M 1/1  
S2C-SMT 3.50/08/180LF 1.5



M 1/1  
S2C-SMT 3.50/08/180LF 3.5



allgemeingültige Kundenzeichnung, aktueller Stand nur auf Anfrage  
general customer drawing, topical version only if required

For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone.  
The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 664 / VDE 0110.  
The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller PCB components are tested to the DIN EN 61984 standard, and are valid for its field of application.  
Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

|                 |         |           |                    |
|-----------------|---------|-----------|--------------------|
| 36              | 59.5    | 2.343     | ±0.2               |
| 34              | 56.0    | 2.205     |                    |
| 32              | 52.5    | 2.067     |                    |
| 30              | 49.0    | 1.929     |                    |
| 28              | 45.5    | 1.791     | ±0.15              |
| 26              | 42.0    | 1.654     |                    |
| 24              | 38.5    | 1.516     |                    |
| 22              | 35.0    | 1.378     |                    |
| 20              | 31.5    | 1.240     | ±0.1               |
| 18              | 28.0    | 1.102     |                    |
| 16              | 24.5    | 0.965     |                    |
| 16              | 24.5    | 0.965     |                    |
| 14              | 21.0    | 0.827     |                    |
| 12              | 17.5    | 0.689     |                    |
| 10              | 14.0    | 0.551     |                    |
| 8               | 10.5    | 0.413     |                    |
| 6               | 7.00    | 0.276     |                    |
| 4               | 3.50    | 0.138     |                    |
| n POLZAHL POLES | L1 [mm] | L1 [inch] | TOLERANZ TOLERANCE |

GENERAL TOLERANCE:  
DIN ISO 2768-m

Max. nos.

99681/4  
22.03.18 AMANN\_A 01  
Modification

**Weidmüller**

Cat.no.:  
**3 50160**   
Drawing no. Issue no.  
Sheet 03 of 04 sheets



Scale: 2/1

Supersedes: .

|             |            |            |
|-------------|------------|------------|
| Drawn       | 15.07.2011 | FRIELING_L |
| Responsible |            | AMANN_A    |
| Checked     | 04.04.2018 | HELIS_MA   |
| Approved    |            | LANG_T     |

**S2C-SMT 3.50/.../...**  
STIFTELEISTE  
MALE HEADER

Product file: B2CF/S2C

7400

## Recommended wave soldering profiles

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

### Single Wave:



### Double Wave:



### Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of  $260\text{ °C}$ . In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.

## Recommended reflow soldering profile

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



## Reflow soldering profile

The perfect soldering profile for SMT Surface Mount Technology is one the most exiting question in SMT production. But there are more than one correct answer: The diagram of temperature-on-time is related to processing features of solder paste and to maximum load of components.

We have to consider the following parameters:

- Time for pre heating
- Maximum temperature
- Time above melting point
- Time for cooling
- Maximum heating rate
- Maximum cooling rate

We recommend a typical solder profile with associated process limits. With preheating components and board are prepared smoothly for the solder phase. Heating rate is typically  $\leq +3\text{K/s}$ . In parallel the solder paste is 'activated'. The time above melting point of 217°C the paste gets liquid and components and boards begin to connect. The maximum temperature of 245°C to 254°C should stay between 10 and 40 seconds. In the cooling phase at  $\geq -6\text{K/s}$  solder is cured. Board and components cool down while avoiding cold cracks.