

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



High-end power supplies must perform efficiently and reliably, even in challenging industrial environments. This requires high power reserves, a long service life and optimal protection against overvoltage, vibration and extreme temperature conditions.

New DCL technology gives PROtop an outstanding dynamic range. This can be used for the reliable triggering of circuit breakers or for powerful motor starts.

General ordering data

Type	PRO TOP1 120W 24V 5A F
Order No.	2568980000
Version	Power supply, switch-mode power supply unit, 24 V
GTIN (EAN)	4050118579703
Qty.	1 pc(s).

PRO TOP1 120W 24V 5A F**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	35 mm	Width (inches)	1.378 inch
Height	130 mm	Height (inches)	5.118 inch
Depth	125 mm	Depth (inches)	4.921 inch
Net weight	850 g		

Temperatures

Humidity at operating temperature	5...95 %, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-25 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C	Operating temperature	-25 °C...70 °C
Storage temperature	-40 °C...85 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Input

AC input voltage range	85...277 V AC	Connection system	PUSH IN with actuator
DC input voltage range	48...410 V DC (Derating 40% @ 48 V DC)	Dielectric strength	max. 300 V AC ≤ 15 s
Frequency range AC	45...65 Hz	Input fuse (internal)	Yes
Inrush current	max. 5 A	Rated input voltage	100 - 240 V AC / 120 - 340 V DC
Recommended back-up fuse	5 A, DI / 6 A, Char. B / 6 A, Char C	Surge protection	Varistor

output

DCL - peak load reserve	150 % (5 s); 600 % (12 ms)	Connection system	PUSH IN with actuator
Mains failure bridge-over time	> 20 ms @ 115V AC/ 230 VAC	Nominal output current for U_{nom}	5 A @ 60 °C
Output power	120 W	Output voltage	24 V
Output voltage	22.5...29 V	Parallel connection option	yes, max 10
Protection against inverse voltage	Yes	Ramp-up time	≤ 100 ms
Rated output voltage	24 V DC ± 1 %	Reserve capacity @ $U_{Nominal}$	130% permanent at ≤ 40°C, 150 % (5 s)
Residual ripple, breaking spikes	< 50 mVss @ U_{Nennr} , Full Load	Triggerable circuit breakers	C2

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

General data

AC failure bridging time @ I_{nom}	> 20 ms @ 230 V AC / > 20 ms @ 115 V AC	Degree of efficiency	91%
Derating	> 60°C (2.5% / 1°C)	Earth leakage current, max.	3.5 mA
Housing version	Metal, corrosion resistant	MTBF	> 1.000.000 h according IEC 1709 (SN29500)
Mounting position, installation notice	Horizontal on DIN rail TS 35, top and bottom 50 mm clearance for free air flow, 10 mm clearance to neighbouring active subassemblies with full load, 5 mm with passive neighbouring subassemblies, direct row mounting with 90% rated load	Operating temperature	-25 °C...70 °C
Power factor (approx.)	> 0.85	Power loss, idling	5 W
Power loss, nominal load	11.8 W	Protection degree	IP20
Series switching capability	Yes	Short-circuit protection	Yes, internal
Start-up	≥ -40 °C	Surge voltage category	III

EMC / shock / vibration

Noise emission in accordance with EN55032	Class B	Vibration resistance IEC 60068-2-6	2.3 g (on DIN rail), 4 g (with direct mounting)
Interference immunity test acc. to	EN 55032:2015, EN 55024:2010/A1:2015, EN 55035:2017, EN 61000-3-2:2014, EN 61000-6-1:2007, EN 61000-6-2:2005, EN 61000-6-3:2007/A1:2011, EN 61000-6-4:2007/A1:2011	Shock resistance IEC 60068-2-27	30 g in all directions

Insulation coordination

Humidity at operating temperature	5...95 %, no condensation	Insulation voltage output / earth	0.5 kV
Insulation voltage output / earth	3.2 kV	Insulation voltage, input/output	3.5 kV
Pollution severity	2	Protection degree	I, with PE connection
Surge voltage category	III		

Electrical safety (applied standards)

Electrical machine equipment	Acc. to EN60204	For use with electronic equipment	Acc. to EN50178 / VDE0160
Protection against dangerous shock currents	Acc. to VDE0106-101	Protective separation / protection against electrical shock	VDE0100-410 / acc. to DIN57100-410
Safety extra-low voltage	SELV according to EN 60950, PELV according to EN 60204	Safety transformers for switch-mode power supplies	according to EN 61558-2-16

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Connection data (input)

Conductor cross-section, AWG/kcmil , max.	12	Conductor cross-section, AWG/kcmil , min.	20
Conductor cross-section, flexible , min.	0.5 mm ²	Conductor cross-section, rigid , max.	1.5 mm ²
Conductor cross-section, rigid , min.	0.5 mm ²	Connection system	PUSH IN with actuator
Number of terminals	3 for L/N/PE	Screwdriver blade	0.6 x 3.5
Wire connection cross section, flexible (input), max.	2.5 mm ²		

Connection data (output)

Conductor cross-section, AWG/kcmil , max.	12	Conductor cross-section, AWG/kcmil , min.	26
Conductor cross-section, flexible , max.	2.5 mm ²	Conductor cross-section, flexible , min.	0.2 mm ²
Conductor cross-section, rigid , max.	2.5 mm ²	Conductor cross-section, rigid , min.	0.2 mm ²
Connection system	PUSH IN with actuator	Number of terminals	4 (++ / -)
Screwdriver blade	0.6 x 3.5		



Connection data (signal)

Wire connection cross-section, flexible (signal), max.	1.5 mm ²	Wire connection cross-section, flexible (signal), min.	0.14 mm ²
Wire connection method	PUSH IN	Wire cross-section, AWG/kcmil , max.	16
Wire cross-section, AWG/kcmil , min.	26	Wire cross-section, solid , max.	1.5 mm ²
Wire cross-section, solid , min.	0.14 mm ²		

Signalling

LED green/red	Green: Operation (failure-free), Flashing green: advance warning $I > 90\%$, Green/red flashing: output switched off (switch-off mode), Flashing red: overload/error
---------------	---

Approvals

Institute (cULus)		Certificate no. (cULus)	E258476
Institute (cULusEX)		Certificate no. (cULusEX)	E470829

Classifications

ETIM 6.0	EC002540	eClass 6.2	27-04-90-04
eClass 9.0	27-04-07-01	eClass 9.1	27-04-07-01

Data sheet**PRO TOP1 120W 24V 5A F**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS

Conform

DownloadsApproval/Certificate/Document of
Conformity[DE_PA5600_18Q206_001.pdf](#)

Engineering Data

[STEP](#)

User Documentation

[Operating instruction](#)

Data sheet

PRO TOP1 120W 24V 5A F

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

