

MetalliCard
CC-M 10/30 2X2.5 AL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	CC-M 10/30 2X2.5 AL
Order No.	1483780000
Version	MetalliCard, Device markers, 10 x 30 mm, silver
GTIN (EAN)	4050118292862
Qty.	200 pc(s).
compatible printer	1324380000

MetalliCard
CC-M 10/30 2X2.5 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	30 mm	Width (inches)	1.181 inch
Height	10 mm	Height (inches)	0.394 inch
Depth	0.5 mm	Depth (inches)	0.02 inch
Net weight	0.45 g		

General data

Colour	silver	Material	Chrome coated aluminium (AL)
Operating temperature range	-55...130 °C	Recommended industries	Energy, Process
Width	30 mm		

Device markers

Drill-hole diameter	2.5 mm
---------------------	--------

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001288
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

MetalliCard CC-M 10/30 2X2.5 AL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

Example of use

