

**HSS-HF 3.2-6.4 EL W13M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The continuous shrink sleeves of the MultiMark series are printed in seconds using our thermo-transfer printers. The length of the marker can be individually adjusted to suit the number of characters or available space. The required length is pre-perforated precisely using a special blade. With their oval shape the markers can be opened easily, applied quickly and shrunk precisely to fit the conductor. An external reel holder (1302920000) has to be used for reels above 30 m printing material.

**General ordering data**

|                    |                                                                                  |
|--------------------|----------------------------------------------------------------------------------|
| Type               | HSS-HF 3.2-6.4 EL W13M                                                           |
| Order No.          | <a href="#">1423360000</a>                                                       |
| Version            | Conductor and cable markers, 3.2 - 6.4 mm, x 10.7 mm, white                      |
| GTIN (EAN)         | 4050118227666                                                                    |
| Qty.               | 1 pc(s).                                                                         |
| compatible printer | <a href="#">2430920000</a> <a href="#">2448870000</a> <a href="#">1140490000</a> |

**HSS-HF 3.2-6.4 EL W13M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |           |                 |             |
|------------|-----------|-----------------|-------------|
| Length     | 13,000 mm | Length (inches) | 511.81 inch |
| Width      | 10.7 mm   | Width (inches)  | 0.421 inch  |
| Depth      | 0.9 mm    | Depth (inches)  | 0.035 inch  |
| Net weight | 190 g     |                 |             |

**General data**

|                 |           |                             |              |
|-----------------|-----------|-----------------------------|--------------|
| Colour          | white     | Halogen                     | No           |
| Length          | 13,000 mm | Material                    | Polyolefine  |
| Number per roll | 1         | Operating temperature range | -55...105 °C |
| Width           | 10.7 mm   |                             |              |

**Conductor and cable markers**

|                               |                     |                                   |                   |
|-------------------------------|---------------------|-----------------------------------|-------------------|
| Conductor O.D.                | 3.2 - 6.4 mm        | Conductor O.D., max.              | 6.4 mm            |
| Conductor O.D., min.          | 3.2 mm              | Conductor cross-section, max.     | 6 mm <sup>2</sup> |
| Conductor cross-section, min. | 1.5 mm <sup>2</sup> | Halogen                           | No                |
| Rate of shrinkage             | 2:1                 | Recommended shrinking temperature | 90 °C             |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC001288    | ETIM 6.0   | EC001530    |
| eClass 6.2 | 27-40-04-01 | eClass 7.1 | 27-14-91-29 |
| eClass 8.1 | 27-14-91-29 | eClass 9.0 | 27-40-04-01 |
| eClass 9.1 | 27-40-04-01 |            |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                                             |                                                                                                                                               |
|---------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">NFX 70-100-1 2006 + NF X 70-100-2 2006</a><br><a href="#">BS EN 45545-2 2013+A1 2015</a><br><a href="#">BS EN ISO 4589-2 1999</a> |
| Engineering Data                            | <a href="#">EPLAN, WSCAD</a>                                                                                                                  |
| Software                                    | <a href="#">M-Print PRO configuration file</a>                                                                                                |

**HSS-HF 3.2-6.4 EL W13M**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

