

VPU series
VPU I 0 N-PE 440V/100KA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Spare arrester Type I**

Weidmüller VPU I surge protection products protect low-voltage consumer installations and electronic devices against overvoltages that can occur as a result of atmospheric discharges (thunderstorms) or switching operations (transients). The VPU I series meets the Type I and Type II requirements acc. to IEC 61643-11 and the Type 1 and Type 2 requirements acc. to EN 61643-11. The spare arresters are coded and can only be inserted into suitable bases.

General ordering data

Type	VPU I 0 N-PE 440V/100KA
Order No.	1351990000
Version	Surge voltage arrester, Low voltage, Accessories, Spare arrester, TT nur für N-PE
GTIN (EAN)	4050118158229
Qty.	1 pc(s).

VPU series
VPU I 0 N-PE 440V/100kA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	35.6 mm	Width (inches)	1.402 inch
Height	94 mm	Height (inches)	3.701 inch
Depth	64 mm	Depth (inches)	2.52 inch
Net weight	140 g		

Temperatures

Humidity	5 - 95% rel. humidity	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	80 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...80 °C		

General data

Colour	blue	Design	Insta IP 20
Optical function display	No	Protection degree	IP20
Segment	Power distribution	UL 94 flammability rating	V-0
Version	Spare arrester		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	IV
--------------------	---	------------------------	----

Rated data IEC / EN

Discharge current $I_{\max}$ (8/20 μ s) N-PE	100 kA	Discharge current I_n (8/20 μ s) N-PE	100 kA
Frequency range, max.	60 Hz	Frequency range, min.	50 Hz
Fuse	Not required	Leakage current at U_n	0 μ A
Lightning test current, I_{imp} (10/350 μ s) (N-PE)	100 kA	Low voltage network	TT nur für N-PE
Max. continuous voltage, U_c (N-PE)	440 V	No. of poles	2
Protection level U_p at I_N (N-PE)	≤ 3 kV	Rated voltage (AC)	400 V
Requirements category acc. to IEC 61643-11	Type I, Type II	Requirements class, acc. to EN 61643-11	T1, T2
Response time	≤ 100 ns	Standards	IEC61643-11, EN61643-11
Temporary surge voltage (over-voltage) - TOV	1,200 V	Voltage type	AC

Connection data

Type of connection	pluggable
--------------------	-----------

Classifications

ETIM 3.0	EC000381	ETIM 5.0	EC000510
ETIM 6.0	EC000941	UNSPSC	30-21-19-22
eClass 5.1	27-14-02-01	eClass 6.2	27-13-08-02
eClass 7.1	27-14-02-01	eClass 8.1	27-14-02-01
eClass 9.0	27-13-08-05	eClass 9.1	27-13-08-05

VPU series VPU I O N-PE 440V/100KA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Downloads


Approval/Certificate/Document of Conformity	CE PAPER Declaration of Conformity
Engineering Data	EPLAN, WSCAD

VPU series VPU I 0 N-PE 440V/100KA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Electric symbol



Schematic circuit diagram