

W-Series
WPD 103 2X70/2X50 GN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Power distribution**

You safely and efficiently distribute electricity to the power consumers with our W-Series feed-through terminal blocks and our optimised WPD phase distribution blocks.

General ordering data

Type	WPD 103 2X70/2X50 GN
Order No.	1561790000
Version	W-Series, Distribution block, Rated cross-section: Screw connection, Terminal rail / mounting plate
GTIN (EAN)	4050118366587
Qty.	3 pc(s).

W-Series
WPD 103 2X70/2X50 GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	32.8 mm	Width (inches)	1.291 inch
Height	63 mm	Height (inches)	2.48 inch
Depth	53.3 mm	Depth (inches)	2.098 inch
Net weight	171 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	130 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Material	Wemid	Colour	green
UL 94 flammability rating	V-0		

System specifications

Version		Tightening torque (clamping screw for aluminium conductors)	4 Nm (25 mm ²) / 8 Nm (35 mm ²) / 10 Nm (50 mm ²) / 18 Nm (70 mm ²)
	Screw connection		
Tightening torque (clamping screw for copper conductors)	10 Nm (70 mm ²) / 6 Nm (50 mm ²)	End cover plate required	No
Number of potentials	1	Number of levels	1
No. of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	Yes	PE connection	No
N-function	No	PE function	No
PEN function	No		

Additional technical data

Installation advice	Terminal rail / mounting plate	Open sides	closed
Snap-on	Yes	Type of mounting	Snap-on
With snap-in pegs	Yes		

Conductors for clamping (rated connection)

Connection direction	on side	Type of connection	Screw connection
----------------------	---------	--------------------	------------------

Rating data

Rated voltage	1,000 V	Rated AC voltage	1,000 V AC
Rated DC voltage	1,000 V DC	Rated current	300 A
Current at maximum wires	300 A	Standards	IEC 60947-7-1, IEC 61238-1, VDE 0603-2

UL rating data

Certificate No. (cURus)	E60693
-------------------------	--------

W-Series

WPD 103 2X70/2X50 GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Classifications

ETIM 5.0	EC001329	ETIM 6.0	EC000897
eClass 6.2	27-14-11-20	eClass 7.1	27-14-11-20
eClass 8.1	27-14-11-20	eClass 9.0	27-14-11-20
eClass 9.1	27-14-11-20		

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	DE_PT1001_20160420_014_ISSUE01.pdf
Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN.WSCAD
Engineering Data	STEP


Safety note

Safety notice	Safety Information
---------------	------------------------------------

W-Series WPD 103 2X70/2X50 GN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



Technical data

Inputs

Number of connections
Solid
Stranded
Flexible with ferrule
Ribbon cable
Torque
Clamping screw
Stripping length

Outputs

Number of connections
Solid
Stranded
Flexible with ferrule
Torque
Clamping screw
Stripping length

No. of poles

Note

IEC 60947-7-1, IEC 61238-1

top	mid./left	mid./mid.	mid./right	bottom
	1		1	
	10...70mm ²		6...50mm ²	
	10...70mm ²		6...50mm ²	
	6...50mm ²		4...35mm ²	
	10Nm		6Nm	
	M 10		M 8	
	25mm		20mm	

top	mid./left	mid./mid.	mid./right	bottom
	1		1	
	10...70mm ²		6...50mm ²	
	10...70mm ²		6...50mm ²	
	6...50mm ²		4...35mm ²	
	10Nm		6Nm	
			M 8	
	25mm		20mm	

1

Aluminium conductor 16 mm² = 4.0 Nm; 25 mm² = 4.0 Nm; 35 mm² = 8.0 Nm; 50 mm² = 10.0 Nm; 70 mm² = 18.0 Nm