

## TM-I

### TM-I 12 MC NE WS V0

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are five different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility.

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the SMark laser printer, PrintJet ADVANCED, plotter, MC-Mobilo or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

#### General ordering data

|                    |                                        |
|--------------------|----------------------------------------|
| Type               | TM-I 12 MC NE WS V0                    |
| Order No.          | <a href="#">1434760000</a>             |
| Version            | TM-I, Insert markers, 12 x 4 mm, white |
| GTIN (EAN)         | 4050118239508                          |
| Qty.               | 320 pc(s).                             |
| compatible printer | <a href="#">1324380000</a>             |

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**TM-I**  
**TM-I 12 MC NE WS V0**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Width      | 4 mm   | Width (inches)  | 0.157 inch |
| Height     | 12 mm  | Height (inches) | 0.472 inch |
| Depth      | 1.7 mm | Depth (inches)  | 0.067 inch |
| Net weight | 0.21 g |                 |            |

**General data**

|                             |              |                                              |                           |
|-----------------------------|--------------|----------------------------------------------|---------------------------|
| Colour                      | white        | Halogen                                      | No                        |
| Material                    | Polyamide 66 | Material colour according to resistance code | 9                         |
| Operating temperature range | -40...100 °C | Recommended industries                       | Transportation, Machinery |
| Type of printing            | neutral      | UL 94 flammability rating                    | V-0                       |
| Width                       | 4 mm         |                                              |                           |

**Conductor and cable markers**

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | ETIM 5.0   | EC000128    |
| ETIM 6.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-40-04-01 |
| eClass 7.1 | 27-14-91-03 | eClass 8.1 | 27-14-91-03 |
| eClass 9.0 | 27-40-04-01 | eClass 9.1 | 27-40-04-01 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">EPLAN, WSCAD, Zuken E3.S</a> |
| Engineering Data | <a href="#">STEP</a>                     |

**Data sheet**

**TM-I**  
**TM-I 12 MC NE WS V0**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**