

OMNIMATE Data - RJ45 jacks transformer RJ45G R1V 1.9N4YG/YG TY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



RJ45 transmitter sockets (magnetics) for gigabit applications (1000 base-T) with integrated compensation actively counteracts inductive and capacitive couplings and saves space on the PCB.

The product range encompasses the following designs:

- 90°, lying (horizontal) and 180°, standing (vertical)
- latch up / latch down
- THT, THR or SMD soldering processes
- Wide range of different design types, also with integrated LEDs and shield contact tabs
- Transmission rates of up to 1 Gbps
- Packed either in a tray (TY) or on a roll (tape-on-reel, RL)
- Compatible with modular RJ45 connector according to ANSI / TIA-1096-A and IEC 60603
- Dielectric strength ≥ 1500 V AC RMS (2250 V AC peak value) according to IEEE 802.3
- Dielectric strength ≥ 1500 V AC (peak value) or ≥ 1500 V DC according to IEC 60603
- Compliance with IEEE 802.3 requirements (1000Base-T, 1 Gbps, IEEE 802.3ab or 100Base-Tx, 100 Mbps, IEEE 802.3u)

Properties and advantages:

- Extended temperature range of -40 °C to $+85$ °C for maximum performance
- Reinforced gold layer (30µ") for improved corrosion protection

- At least 3 mm stand-off ensures a perfect soldering result

General ordering data

Type	RJ45G R1V 1.9N4YG/YG TY
Order No.	2562170000
Version	PCB plug-in connector, RJ45 jacks transformer, 1000 Mbps, THT/THR solder connection, 180°, Shield tabs: none, 30-80 µ" Ni / 30- µ" Au, LED: Yes, Green/yellow, No. of poles: 10, Tray (manual assembly)
GTIN (EAN)	4050118570601
Qty.	120 pc(s).
Packaging	Tray (manual assembly)

OMNIMATE Data - RJ45 jacks transformer RJ45G R1V 1.9N4YG/YG TY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	16 mm	Width (inches)	0.63 inch
Height	18.9 mm	Height (inches)	0.744 inch
Height of lowest version	17 mm	Depth	16.8 mm
Depth (inches)	0.661 inch	Net weight	7 g

Temperatures

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-40 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

System specifications

Colour of left LED	Green/yellow	LED	Yes
Mounting onto the PCB	THT/THR solder connection	No. of poles	10
Number of solder pins per pole	1	Outgoing elbow	180°
Pitch in inches (P)	0.05 inch	Pitch in mm (P)	1.27 mm
Plugging cycles	750	Product family	OMNIMATE Data - RJ45 jacks transformer
Protection degree	IP20	Shield surface	nickel-plated
Shield tabs	none	Shielding	Yes
Shielding material	Brass	Transmission rate	1000 Mbps
Type of connection	Socket connector		

Electrical properties

Dielectric strength, contact / contact	1000 V DC	Dielectric strength, contact / shield	1500 V DC
Insulation strength	> 500 MΩ	Rated current	1.5 A
Rated voltage	125 V AC		

Material data

Insulating material	PA 9T	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	II
CTI	≥ 500	Insulation strength	> 500 MΩ
Moisture Level (MSL)	1	UL 94 flammability rating	V-0
Contact base material	Phosphorus bronze	Contact surface	Gold over nickel
Layer structure of plug contact	30-80 μ" Ni / 30- μ" Au	Storage temperature, min.	-40 °C
Storage temperature, max.	85 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	85 °C		

Packing

Packaging	Tray (manual assembly)	VPE length	0.32 m
VPE width	0.19 m	VPE height	0.065 m

Classifications

ETIM 6.0	EC002637	eClass 6.2	27-25-05-04
eClass 9.0	27-44-04-02	eClass 9.1	27-44-04-02

OMNIMATE Data - RJ45 jacks transformer RJ45G R1V 1.9N4YG/YG TY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Approvals

Approvals




ROHS

Conform


Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings


Dimensioned drawing




Dimensioned drawing




Dimensioned drawing




Dimensioned drawing



Dimensioned drawing



PCB design




OMNIMATE Data - RJ45 jacks transformer RJ45G R1V 1.9N4YG/YG TY


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

PCB design



Wiring diagram



OMNIMATE Data - RJ45 jacks transformer

RJ45G R1V 1.9N4YG/YG TY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Drawings

Schematic

Characteristics

Inductance	350 µH min. @ 100 kHz, 100 mV, 8 mA DC Bias
Leakage Inductance	0.3 µH max. @ 100 kHz, 100 mV
Insertion Loss	1.1 dB max. @ (1 - 100) MHz
Return Loss	18 dB min. @ (1 - 30) MHz 16 dB min. @ (30 - 60) MHz 12 dB min. @ (60 - 80) MHz
Cross Talk	30 dB min. @ (1 - 100) MHz
Common Mode Rejection	30 dB min. @ (1 - 100) MHz

Type codes

RJ45	G1	R	1	U	3.2	E	4	GY/GY	TY	RJ45G1 R1U 3.2E4GY/GY TY																																																																																																																		
										<table><tr><td>Packaging</td><td>TY</td><td>Tray in box (manual assembly)</td></tr><tr><td></td><td>RL</td><td>Tape on Reel (automated assembly)</td></tr><tr><td>LED</td><td>Y/G</td><td>Yellow/Green</td></tr><tr><td></td><td>G/Y</td><td>Green/Yellow (standard)</td></tr><tr><td></td><td>GY/GY</td><td>Green-Yellow/Green-Yellow</td></tr><tr><td></td><td>O/G</td><td>Orange/Green</td></tr><tr><td></td><td>R/O</td><td>Red/Orange</td></tr><tr><td></td><td>...</td><td>... (further combinations possible)</td></tr><tr><td></td><td>N</td><td>without LED</td></tr><tr><td>Contact surface thickness</td><td>4</td><td>1 = 3µ", 2 = 6µ", 3 = 15µ", 4 = 30µ", 5 = 50µ"</td></tr><tr><td>EMI tabs (ground fingers)</td><td>E</td><td>E = with EMI tabs</td></tr><tr><td></td><td>N</td><td>N = without EMI tabs</td></tr><tr><td>Solder Pin length</td><td>3.2</td><td>3.2 mm</td></tr><tr><td></td><td>1.6</td><td>1.6 mm</td></tr><tr><td></td><td>D</td><td>SMD</td></tr><tr><td>Direction, latch style</td><td>U</td><td>Horizontal (90°, side entry), latch up</td></tr><tr><td></td><td>D</td><td>Horizontal (90°, side entry), latch down</td></tr><tr><td></td><td>V</td><td>Vertical (180°, top entry)</td></tr><tr><td></td><td>Y</td><td>Diagonal (45°), latch up</td></tr><tr><td>Number of Ports</td><td>1</td><td>1 Port</td></tr><tr><td></td><td>12; 14; ...</td><td>multi ports side by side, Multiport</td></tr><tr><td></td><td>2; 4; ...</td><td>multi ports about each other, Multilevel</td></tr><tr><td>Assembly on PCB</td><td>R</td><td>Through Hole Reflow - THR</td></tr><tr><td></td><td>S</td><td>Soldering process: Wave or Reflow soldering</td></tr><tr><td></td><td>T</td><td>Surface Mount Technology - SMT</td></tr><tr><td></td><td></td><td>Soldering process: Reflow soldering</td></tr><tr><td></td><td></td><td>Through Hole Technology - THT</td></tr><tr><td></td><td></td><td>Soldering process: Wave</td></tr><tr><td>Performance Category</td><td>C5</td><td>Category 5</td></tr><tr><td></td><td>C6</td><td>Category 6</td></tr><tr><td></td><td>C6A</td><td>Category 6A</td></tr><tr><td></td><td>C5e</td><td>Category 5e</td></tr><tr><td></td><td>M</td><td>10/100 Mbit</td></tr><tr><td></td><td>G1</td><td>10/100/1000 Mbit</td></tr><tr><td></td><td>G10</td><td>10 Gbit</td></tr><tr><td></td><td>U</td><td>Unshielded</td></tr><tr><td></td><td>MP</td><td>10/100 Mbit with POE</td></tr><tr><td></td><td>MP+</td><td>10/100 Mbit with POE+</td></tr></table>	Packaging	TY	Tray in box (manual assembly)		RL	Tape on Reel (automated assembly)	LED	Y/G	Yellow/Green		G/Y	Green/Yellow (standard)		GY/GY	Green-Yellow/Green-Yellow		O/G	Orange/Green		R/O	Red/Orange		...	... (further combinations possible)		N	without LED	Contact surface thickness	4	1 = 3µ", 2 = 6µ", 3 = 15µ", 4 = 30µ", 5 = 50µ"	EMI tabs (ground fingers)	E	E = with EMI tabs		N	N = without EMI tabs	Solder Pin length	3.2	3.2 mm		1.6	1.6 mm		D	SMD	Direction, latch style	U	Horizontal (90°, side entry), latch up		D	Horizontal (90°, side entry), latch down		V	Vertical (180°, top entry)		Y	Diagonal (45°), latch up	Number of Ports	1	1 Port		12; 14; ...	multi ports side by side, Multiport		2; 4; ...	multi ports about each other, Multilevel	Assembly on PCB	R	Through Hole Reflow - THR		S	Soldering process: Wave or Reflow soldering		T	Surface Mount Technology - SMT			Soldering process: Reflow soldering			Through Hole Technology - THT			Soldering process: Wave	Performance Category	C5	Category 5		C6	Category 6		C6A	Category 6A		C5e	Category 5e		M	10/100 Mbit		G1	10/100/1000 Mbit		G10	10 Gbit		U	Unshielded		MP	10/100 Mbit with POE		MP+	10/100 Mbit with POE+
Packaging	TY	Tray in box (manual assembly)																																																																																																																										
	RL	Tape on Reel (automated assembly)																																																																																																																										
LED	Y/G	Yellow/Green																																																																																																																										
	G/Y	Green/Yellow (standard)																																																																																																																										
	GY/GY	Green-Yellow/Green-Yellow																																																																																																																										
	O/G	Orange/Green																																																																																																																										
	R/O	Red/Orange																																																																																																																										
	...	... (further combinations possible)																																																																																																																										
	N	without LED																																																																																																																										
Contact surface thickness	4	1 = 3µ", 2 = 6µ", 3 = 15µ", 4 = 30µ", 5 = 50µ"																																																																																																																										
EMI tabs (ground fingers)	E	E = with EMI tabs																																																																																																																										
	N	N = without EMI tabs																																																																																																																										
Solder Pin length	3.2	3.2 mm																																																																																																																										
	1.6	1.6 mm																																																																																																																										
	D	SMD																																																																																																																										
Direction, latch style	U	Horizontal (90°, side entry), latch up																																																																																																																										
	D	Horizontal (90°, side entry), latch down																																																																																																																										
	V	Vertical (180°, top entry)																																																																																																																										
	Y	Diagonal (45°), latch up																																																																																																																										
Number of Ports	1	1 Port																																																																																																																										
	12; 14; ...	multi ports side by side, Multiport																																																																																																																										
	2; 4; ...	multi ports about each other, Multilevel																																																																																																																										
Assembly on PCB	R	Through Hole Reflow - THR																																																																																																																										
	S	Soldering process: Wave or Reflow soldering																																																																																																																										
	T	Surface Mount Technology - SMT																																																																																																																										
		Soldering process: Reflow soldering																																																																																																																										
		Through Hole Technology - THT																																																																																																																										
		Soldering process: Wave																																																																																																																										
Performance Category	C5	Category 5																																																																																																																										
	C6	Category 6																																																																																																																										
	C6A	Category 6A																																																																																																																										
	C5e	Category 5e																																																																																																																										
	M	10/100 Mbit																																																																																																																										
	G1	10/100/1000 Mbit																																																																																																																										
	G10	10 Gbit																																																																																																																										
	U	Unshielded																																																																																																																										
	MP	10/100 Mbit with POE																																																																																																																										
	MP+	10/100 Mbit with POE+																																																																																																																										

Recommended wave soldering profiles

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Single Wave:



Double Wave:



Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260 °C . In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.

Recommended reflow soldering profile

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Reflow soldering profile

The perfect soldering profile for SMT Surface Mount Technology is one the most exiting question in SMT production. But there are more than one correct answer: The diagram of temperature-on-time is related to processing features of solder paste and to maximum load of components.

We have to consider the following parameters:

- Time for pre heating
- Maximum temperature
- Time above melting point
- Time for cooling
- Maximum heating rate
- Maximum cooling rate

We recommend a typical solder profile with associated process limits. With preheating components and board are prepared smoothly for the solder phase. Heating rate is typically $\leq +3\text{K/s}$. In parallel the solder paste is 'activated'. The time above melting point of 217°C the paste gets liquid and components and boards begin to connect. The maximum temperature of 245°C to 254°C should stay between 10 and 40 seconds. In the cooling phase at $\geq -6\text{K/s}$ solder is cured. Board and components cool down while avoiding cold cracks.