

**Klippon EBi QL (Essential Box industrial - Quarter Lock)
KEBI QL 604022 S2B1**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For many years, the name Klippon® has stood for competence and quality in enclosures.

The Klippon® EBi industrial enclosure series protects your components reliably if they are used in moderate environmental conditions and is designed for everyday applications.

With the ever-increasing need for individual application solutions, the Klippon® EBi with its high degree of protection and impact resistance is ideally suited to your needs.

Our standard product is the Klippon® EBi QL – with hinged door and double-bit key lock.

A variant with mounting screws is also available, but is only manufactured on request and is subject to a minimum order quantity. DNV GL and cULus approvals are also available on request.

General ordering data

Type	KEBI QL 604022 S2B1
Order No.	2470880000
Version	Klippon EBi QL (Essential Box industrial - Quarter Lock), Empty enclosure, stainless steel enclosure, Height: 600 mm, Width: 400 mm, Depth: 220 mm, Gland plates: Bottom, Material: Stainless steel 1.4301 (304), Brushed, silver
GTIN (EAN)	4050118591217
Qty.	1 pc(s).

Klippon EBi QL (Essential Box industrial - Quarter Lock) KEBI QL 604022 S2B1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	400 mm	Width (inches)	15.748 inch
Height	600 mm	Height (inches)	23.622 inch
Depth	220 mm	Depth (inches)	8.661 inch
Mounting dimension - width	350 mm	Mounting dimension - height	550 mm
Wall thickness, max.	2 mm	Wall thickness, min.	2 mm
Net weight	11,240,000 g	Diameter	9 mm

Certificate numbers enclosure

Certificate no. (cULus)	E243298
-------------------------	---------

General information

Areas of use	Harbour facilities, Machine construction, Transportation, Marine engineering, Packaging industry, Process industry	Flange plate mounting	
Gland plates	Bottom	Installation advice	M5 Torx stainless-steel screws TX20 Welded assembly angle, Mounting plate
Material thickness	1.5 mm	Material thickness of cover	1.5 mm
Material thickness of enclosure	1.5 mm	Material thickness of flange	1.5 mm
Opening angle lid	125 °	Seal material of cover	Polyurethane foamed
Seal material of flange plate	EPDM	Standards	DIN EN 62208, IEC 60529
Material	Stainless steel 1.4301 (304)	Seal material	Polyurethane foamed, EPDM
Surface finish	Brushed	Operating temperature, min.	-40 °C
Operating temperature, max.	85 °C	Impact resistance	10.00 J
Protection degree	IP66	Enclosure attachment	Fixing lugs, Installation through the housing rear wall
Lid attachment	Quarter-turn fastener with slotted insert	Integral fixing	Screwed

Housing earth

Earth, enclosure, cover	Welded-on M6 stainless- steel earth stud in enclosure body and lid.	Earth, enclosure, external	M6 earth tab rivet
Earth, enclosure, internal	Welded-on M6 stainless- steel earth stud in enclosure body and lid.		

Classifications

ETIM 6.0	EC000261	eClass 6.2	27-14-91-07
eClass 9.0	27-18-01-01	eClass 9.1	27-18-92-90

Approvals

Approvals



ROHS Conform

Creation date May 27, 2019 7:37:57 PM CEST

Catalogue status 23.05.2019 / We reserve the right to make technical changes.

Klippon EBi QL (Essential Box industrial - Quarter Lock)
KEBI QL 604022 S2B1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Downloads

Engineering Data

[STEP](#)

Klippon EBi QL (Essential Box industrial - Quarter Lock)
KEBI QL 604022 S2B1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing

