

VPU series
VPU AC I 3 R 440/25 LCF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller VPU I (Type I), VPU II (Type II) and VPU III (Type III) surge protection products effectively reduce the interference coupling that can occur due to transient surge voltages, even significantly below the limits prescribed by insulation co-ordination according to EN 60664-3 / DIN VDE 0110-3. This means that the whole installation is exposed to fewer malfunctions. The arresters are co-ordinated using technical means. This means that decoupling between Types I, II and III is unnecessary. The arresters are tested according to product standard IEC 61643-11 / DIN EN 61643-11 and can be installed in systems according to IEC 61643-12 / VDE V0675-6-12 and IEC 62305-4 / VDE 0185-4. This lightning and surge protection device is suited for installation in power supply systems. Weidmüller offers different products depending on the particular mains network type and voltage level. A special Type I and Type II protective device is even available for photovoltaic applications.

General ordering data

Type	VPU AC I 3 R 440/25 LCF
Order No.	2619170000
GTIN (EAN)	4050118634617
Qty.	1 pc(s).

VPU series
VPU AC I 3 R 440/25 LCF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	108 mm	Width (inches)	4.252 inch
Height	106 mm	Height (inches)	4.173 inch
Depth	93 mm	Depth (inches)	3.661 inch
Net weight	25 g		

Temperatures

Humidity	5 - 95% rel. humidity	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...85 °C
Storage temperature	-40 °C...85 °C		

Connection data, remote alert

Connection type	Screw connection, pluggable	Stripping length	8 mm
Cross-section for connected wire, solid core, min.	0.14 mm ²	Cross-section for connected wire, solid core, max.	1.5 mm ²

General data

Altitude	≤ 2000 m	Colour	black
Design	Installation housing; 6 TE, Insta IP 20	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP20 in installed state	Rail	TS 35
Segment	Power distribution	Suitable for	Count-in installation (leakage current free)
UL 94 flammability rating	V-0	Version	Surge protection, with remote contact

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

VPU series
VPU AC I 3 R 440/25 LCF
Weidmüller Interface GmbH & Co. KG

 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Rated data IEC / EN

Discharge current $I_{\max}$ (8/20 μ s) wire-PE	100 kA	Discharge current I_n (8/20 μ s) wire-PE	25 kA
Follow-on current extinguishing capability I_{fi}	Not available due for technical reasons	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Fuse	250 A gL (if back up fuse > 250 A)
Leakage current at U_n	5 μ A	Lightning test current I_{imp} (10/350 μ s) (L-PE)	25 kA
Low voltage network	TN-C	Max. continuous voltage, U_c (AC)	440 V
No. of poles	6	Protection level U_p (typ.)	≤ 2.5 kV
Protection level U_p at I_N (L/N-PE)	≤ 2.5 kV	Rated load current I_L	100 A
Rated voltage (AC)	400 V	Requirements category acc. to IEC 61643-11	Type I, Type II
Requirements class, acc. to EN 61643-11	T1, T2	Response time	≤ 25 ns
Short-circuit current rating I_{SCCR}	50 kA	Signalling contact	250 V 1A 1CO
Standards	IEC61643-11, EN61643-11, EN60068-2-27:2009, EN60068-2-64:2008, EN60068-2-6:2008	Suitable for	Count-in installation (leakage current free)
Temporary surge voltage (over-voltage) - TOV	762 V	Voltage type	AC

Connection data

Wire connection method	Screw connection	Type of connection	Screw connection
Stripping length, rated connection	13 mm	Tightening torque, min.	2 Nm
Tightening torque, max.	3 Nm	Clamping range, rated connection	16 mm ²
Clamping range, min.	6 mm ²	Clamping range, max.	35 mm ²
Wire cross-section, solid, min.	6 mm ²	Wire cross-section, solid, max.	16 mm ²
Wire connection cross-section, finely stranded, min.	6 mm ²	Wire connection cross section, finely stranded, max.	25 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	6 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	35 mm ²
Connection cross-section, stranded, min.	6 mm ²	Connection cross-section, stranded, max.	35 mm ²

Classifications

ETIM 3.0	EC000381	ETIM 5.0	EC000510
ETIM 6.0	EC000941	UNSPSC	30-21-19-22
eClass 5.1	27-14-02-01	eClass 6.2	27-13-08-02
eClass 7.1	27-14-02-01	eClass 8.1	27-14-02-01
eClass 9.0	27-13-08-05	eClass 9.1	27-13-08-05

Approvals

Approvals



ROHS

Conform

Data sheet**VPU series
VPU AC I 3 R 440/25 LCF**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Downloads**


Approval/Certificate/Document of Conformity	Declaration of Conformity Declaration of Conformity Declaration of Conformity Declaration of Conformity
Engineering Data	STEP

VPU series VPU AC I 3 R 440/25 LCF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Electric symbol



Schematic circuit diagram