
# HS 6.4-19.1/25 MM W

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



**MultiMark**
With MultiMark you have a fast and reliable marking system at your disposal to enable virtually any kind of marking. Connectors, conductors, cables or devices – the MultiMark product family offers a well-structured, practical range of markers which can be used in combination with our advanced M-Print® PRO configuration software for all areas of use.

**Your benefits with MultiMark**
- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

## General ordering data

| | |
|---|---|
| Type | HS 6.4-19.1/25 MM W |
| Order No. | 2437750000 |
| Version | Conductor and cable markers, 6.4 - 19.1 mm, 25.4 x 30.9 mm, white |
| GTIN (EAN) | 4050118458008 |
| Qty. | 800 pc(s). |
| compatible printer | 2430920000 2448870000 1140490000 |

# HS 6.4-19.1/25 MM W

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Technical data

### Dimensions and weights

| | | | |
|---|---|---|---|
| Width | 30.9 mm | Width (inches) | 1.217 inch |
| Height | 25.4 mm | Height (inches) | 1 inch |
| Depth | 0.77 mm | Depth (inches) | 0.03 inch |
| Net weight | 0.8 g | | |

### General data

| | | | |
|---|---|---|---|
| Colour | white | Halogen | Yes |
| Material | Polyolefine | Number per roll | 800 |
| Operating temperature range | -55…135 °C | Recommended industries | Plant manufacture, Energy, Device manufacturer, Machinery |
| Width | 30.9 mm | | |

### Conductor and cable markers

| | | | |
|---|---|---|---|
| Conductor O.D. | 6.4 - 19.1 mm | Conductor O.D., max. | 19.1 mm |
| Conductor O.D., min. | 6.4 mm | Conductor cross-section, max. | 70 mm² |
| Conductor cross-section, min. | 16 mm² | Halogen | Yes |
| Rate of shrinkage | 3:1 | Recommended shrinking temperature | 90 °C |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 5.0 | EC001530 | ETIM 6.0 | EC001530 |
| eClass 6.2 | 27-40-04-01 | eClass 9.0 | 27-40-04-01 |
| eClass 9.1 | 27-40-04-01 | | |

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Downloads

| | |
|---|---|
| Engineering Data | EPLAN |

# HS 6.4-19.1/25 MM W

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Drawings

