

**SlimFix X**  
**SFX 10/60 S MC NE GE V0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



SlimFix X are halogen-free conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. SlimFix is an acknowledged and approved marker type in traffic engineering. The SF tool allows easy installation even in case of small markers.

- Halogen-free material
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|                    |                                                                          |
|--------------------|--------------------------------------------------------------------------|
| Type               | SFX 10/60 S MC NE GE V0                                                  |
| Order No.          | <a href="#">2009900000</a>                                               |
| Version            | SlimFix X, Conductor and cable markers, 7 - 40 mm, 60 x 13.62 mm, yellow |
| GTIN (EAN)         | 4050118396294                                                            |
| Qty.               | 50 pc(s).                                                                |
| compatible printer | <a href="#">1324380000</a>                                               |

**SlimFix X**  
**SFX 10/60 S MC NE GE V0**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Width      | 13.62 mm | Width (inches)  | 0.536 inch |
| Height     | 60 mm    | Height (inches) | 2.362 inch |
| Depth      | 1 mm     | Depth (inches)  | 0.039 inch |
| Net weight | 2.367 g  |                 |            |

**General data**

|                         |                              |                             |               |
|-------------------------|------------------------------|-----------------------------|---------------|
| Colour                  | yellow                       | Halogen                     | No            |
| Material                | Polyamide 66                 | Operating temperature range | -40... 100 °C |
| Size of labelling field | 60 x 9.5 mm                  | UL 94 flammability rating   | V-0           |
| Version                 | Installation with cable ties | Width                       | 13.62 mm      |

**Conductor and cable markers**

|                               |                    |                               |                     |
|-------------------------------|--------------------|-------------------------------|---------------------|
| Conductor O.D.                | 7 - 40 mm          | Conductor O.D., max.          | 40 mm               |
| Conductor O.D., min.          | 7 mm               | Conductor cross-section, max. | 500 mm <sup>2</sup> |
| Conductor cross-section, min. | 16 mm <sup>2</sup> | Halogen                       | No                  |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 5.0   | EC001530    | ETIM 6.0   | EC001530    |
| eClass 6.2 | 27-40-04-01 | eClass 9.0 | 27-40-04-01 |
| eClass 9.1 | 27-40-04-01 |            |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |                              |
|------------------|------------------------------|
| Engineering Data | <a href="#">EPLAN, WSCAD</a> |
|------------------|------------------------------|