

VPU series
VPU II 2 R PV 1000V DC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Type II surge voltage arrester for use in photovoltaic applications**

- Pluggable arrester
- Suitable for protecting DC systems
- High energy absorption with short response time
- Tested in accordance with EN 50539-11
- Suitable for use in accordance with IEC 60364-7-712 / EN 50539-12
- Coded voltage level
- Installation in distribution board
- Thermal protection function

General ordering data

Type	VPU II 2 R PV 1000V DC
Order No.	1351240000
Version	Surge voltage arrester, Low voltage, 1000 V, with remote contact, 25 kA
GTIN (EAN)	4050118158816
Qty.	1 pc(s).

VPU series

VPU II 2 R PV 1000V DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	35.6 mm	Width (inches)	1.402 inch
Height	106 mm	Height (inches)	4.173 inch
Depth	69 mm	Depth (inches)	2.717 inch
Mounting dimension - height	75 mm	Net weight	288 g

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	80 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C	Storage temperature	-40 °C...80 °C

Connection data, remote alert

Connection type	PUSH IN	Stripping length	8 mm
Cross-section for connected wire, solid core, min.	0.14 mm ²	Cross-section for connected wire, solid core, max.	1.5 mm ²

General data

Colour	black, orange	Design	Installation housing; 2TE, Insta IP 20
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
Rail	TS 35	UL 94 flammability rating	V-0
Version	with remote contact		

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Photovoltaic technical data

Conditions and requirements	EN 50539-11	Discharge current I_n (8/20 µs)	12.5 kA
Discharge current, max. (8/20 µs)	25 kA	Maximum continuous operating voltage UCPV mode +/-, -/PE, +/-PE	1,000 V DC
PV system voltage, max. U_{cpv}	1,000 V	Protection level U_p mode (+/-)	≤ 5.6 kV
Protection level U_p mode (-/PE)	≤ 2.8 kV	Protection level U_p mode(+/-PE)	≤ 2.8 kV
Requirements class	Type II	Short-circuit current I_{SCPv}	200 A
Standards	EN 50539-11		

Connection data

Type of connection	Screw connection	Stripping length, rated connection	15 mm
Tightening torque, min.	2 Nm	Tightening torque, max.	3 Nm
Clamping range, rated connection	16 mm ²	Clamping range, min.	1.5 mm ²
Clamping range, max.	35 mm ²	Wire cross-section, solid, min.	1.5 mm ²
Wire cross-section, solid, max.	16 mm ²	Wire connection cross-section, finely stranded, min.	1.5 mm ²
Wire connection cross section, finely stranded, max.	25 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), min.	1.5 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), max.	50 mm ²	Connection cross-section, stranded, min.	1.5 mm ²
Connection cross-section, stranded, max.	50 mm ²		

VPU series

VPU II 2 R PV 1000V DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Classifications

ETIM 3.0	EC000941	ETIM 5.0	EC000510
ETIM 6.0	EC000941	UNSPSC	30-21-19-21
eClass 5.1	27-13-08-01	eClass 6.2	27-13-08-02
eClass 7.1	27-14-02-01	eClass 8.1	27-14-02-01
eClass 9.0	27-13-08-05	eClass 9.1	27-13-08-05

Approvals

Approvals



ROHS

Conform

Downloads


Approval/Certificate/Document of Conformity	CE PAPER Declaration of Conformity Declaration of Conformity
Brochure/Catalogue	CAT 4.4 ELECTR 16/17 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
User Documentation	Instruction sheet

VPU series VPU II 2 R PV 1000V DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Electric symbol



Circuit diagram