

## PROtop PRO TOP1 120W 12V 10A EX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



High-end power supplies must perform efficiently and reliably, even in challenging industrial environments. This requires high power reserves, a long service life and optimal protection against overvoltage, vibration and extreme temperature conditions.

New DCL technology gives PROtop an outstanding dynamic range. This can be used for the reliable triggering of circuit breakers or for powerful motor starts.

### General ordering data

Type	PRO TOP1 120W 12V 10A EX
Order No.	<a href="#">2467020000</a>
Version	Power supply, switch-mode power supply unit, 12 V
GTIN (EAN)	4050118481921
Qty.	1 pc(s).

**PROtop**  
**PRO TOP1 120W 12V 10A EX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	35 mm	Width (inches)	1.378 inch
Height	130 mm	Height (inches)	5.118 inch
Depth	125 mm	Depth (inches)	4.921 inch
Net weight	850 g		

**Temperatures**

Humidity at operating temperature	5...100 % no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...85 °C		

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Input**

AC input voltage range	85...277 V AC	Connection system	Clamping yoke
DC input voltage range	80 ... 410 V DC	Dielectric strength	max. 300 V AC ≤ 15 s
Frequency range AC	45...65 Hz	Input fuse (internal)	Yes
Inrush current	max. 5 A	Rated input voltage	100 - 240 V AC / 120 - 340 V DC
Recommended back-up fuse	5 A, DI / 6 A, Char. B / 6 A, Char C	Surge protection	Varistor

**output**

DCL - peak load reserve	150 % (5 s); 400 % (15 ms)	Connection system	Clamping yoke connection
Mains failure bridge-over time	> 20 ms @ 115V AC/ 230 VAC	Nominal output current for $U_{nom}$	10 A @ 60 °C
Output power	120 W	Output voltage	12 V
Output voltage	11...15 V	Parallel connection option	yes, max 10
Protection against inverse voltage	Yes	Ramp-up time	≤ 100 ms
Rated output voltage	12 V DC ± 1 %	Reserve capacity @ $U_{Nominal}$	130% permanent at ≤ 40°C, 150 % (5 s)
Residual ripple, breaking spikes	< 50 mVss @ $U_{Nennr}$ , Full Load	Triggerable circuit breakers	B6, C2

**PROtop**  
**PRO TOP1 120W 12V 10A EX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**General data**

AC failure bridging time @ I <sub>nom</sub>	> 20 ms @ 230 V AC / > 20 ms @ 115 V AC	Conformal coating	Yes
Degree of efficiency	90%	Derating	> 60°C (2.5% / 1°C)
Earth leakage current, max.	3.5 mA	Housing version	Metal, corrosion resistant
MTBF	> 1.000.000 h according IEC 1709 (SN29500)	Mounting position, installation notice	Horizontal on DIN rail TS 35, top and bottom 50 mm clearance for free air flow, 10 mm clearance to neighbouring active subassemblies with full load, 5 mm with passive neighbouring subassemblies, direct row mounting with 90% rated load
Operating temperature	-40 °C...70 °C	Power factor (approx.)	> 0.85
Power loss, idling	5 W	Power loss, nominal load	13.3 W
Protection degree	IP20	Series switching capability	Yes
Short-circuit protection	Yes, internal	Surge voltage category	III

**EMC / shock / vibration**

Noise emission in accordance with EN55032	Class B	Vibration resistance IEC 60068-2-6	2.3 g (on DIN rail), 4 g (with direct mounting)
Interference immunity test acc. to	EN 55032:2015, EN 55024:2010/A1:2015, EN 55035:2017, EN 61000-3-2:2014, EN 61000-6-1:2007, EN 61000-6-2:2005, EN 61000-6-3:2007/A1:2011, EN 61000-6-4:2007/A1:2011	Shock resistance IEC 60068-2-27	30 g in all directions

**Insulation coordination**

Humidity at operating temperature	5...100 % no condensation	Insulation voltage output / earth	0.5 kV
Insulation voltage output / earth	3.2 kV	Insulation voltage, input/output	3.5 kV
Pollution severity	2	Protection degree	I, with PE connection
Surge voltage category	III		

**Electrical safety (applied standards)**

Electrical machine equipment	Acc. to EN60204	For use with electronic equipment	Acc. to EN50178 / VDE0160
Protection against dangerous shock currents	Acc. to VDE0106-101	Protective separation / protection against electrical shock	VDE0100-410 / acc. to DIN57100-410
Safety extra-low voltage	SELV according to EN 60950, PELV according to EN 60204	Safety transformers for switch-mode power supplies	according to EN 61558-2-16

**PROtop  
PRO TOP1 120W 12V 10A EX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Connection data (input)**

Conductor cross-section, AWG/kcmil , max.	12	Conductor cross-section, AWG/kcmil , min.	30
Conductor cross-section, flexible , min.	0.2 mm <sup>2</sup>	Conductor cross-section, rigid , max.	4 mm <sup>2</sup>
Conductor cross-section, rigid , min.	0.2 mm <sup>2</sup>	Connection system	Clamping yoke
Number of terminals	3 for L/N/PE	Screwdriver blade	0.6 x 3.5
Wire connection cross section, flexible (input), max.	4 mm <sup>2</sup>		

**Connection data (output)**

Conductor cross-section, AWG/kcmil , max.	12	Conductor cross-section, AWG/kcmil , min.	30
Conductor cross-section, flexible , max.	4 mm <sup>2</sup>	Conductor cross-section, flexible , min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid , max.	4 mm <sup>2</sup>	Conductor cross-section, rigid , min.	0.2 mm <sup>2</sup>
Connection system	Clamping yoke connection	Number of terminals	5 (+ + / - - -)
Screwdriver blade	0.6 x 3.5		



**Connection data (signal)**

Wire connection cross-section, flexible (signal), max.	1.5 mm <sup>2</sup>	Wire connection cross-section, flexible (signal), min.	0.2 mm <sup>2</sup>
Wire cross-section, AWG/kcmil , max.	16	Wire cross-section, AWG/kcmil , min.	28
Wire cross-section, solid , max.	1.5 mm <sup>2</sup>	Wire cross-section, solid , min.	0.2 mm <sup>2</sup>

**Signalling**

LED green/red	Green: Operation (failure-free), Flashing green: advance warning $I > 90\%$ , Green/red flashing: output switched off (switch-off mode), Flashing red: overload/error
---------------	---

**Approvals**

Institute (cULus)		Certificate no. (cULus)	E258476
Institute (cULusEX)		Certificate no. (cULusEX)	E470829

**Classifications**

ETIM 6.0	EC002540	eClass 6.2	27-04-90-04
eClass 9.0	27-04-07-01	eClass 9.1	27-04-07-01

**Data sheet**

**PROtop  
PRO TOP1 120W 12V 10A EX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of  
 Conformity

[Declaration of Conformity](#)

Engineering Data

[STEP](#)

User Documentation

[IS PRO TOP1 120W 12V 10A EX](#)

**Data sheet**

**PROtop  
PRO TOP1 120W 12V 10A EX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

