

Accessories

CB-DT 200/4.5 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



With our detectable marking solutions, we support our food and beverage industry customers in ensuring the high standards required within the HACCP concept. Due to a metallic filler, our detectable Cable Ties are identified reliably by metal and X-ray detectors. Identification minimises the risk of contamination during the food production process. MultiCards provide maximal safety because of properties like corrosion resistance. We regularly check and confirm the safety properties in our accredited laboratory. Actual colour may vary, the tone does not affect the product characteristics. Not suitable for direct contact with food.

- Detectable by metal and X-ray detectors
- Visually recognisable by blue colour
- Corrosion resistant metallic filler

General ordering data

Type	CB-DT 200/4.5 BL
Order No.	2602770000
GTIN (EAN)	4050118650181
Qty.	100 pc(s).

Data sheet

Accessories CB-DT 200/4.5 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	4.5 mm	Width (inches)	0.177 inch
Height	200 mm	Height (inches)	7.874 inch
Net weight	1.7 g		

Installation materials

Cable diameter, max.	51 mm	Detectible in accordance with Rondotest 0.3 mm Fe	
Material	Polyamide 66	Operating temperature range, max.	85 °C
Operating temperature range, min.	-25 °C	Recommended industries	Food processing industry
Tensile strength	220 N	UL 94 flammability rating	HB
Version	Cable ties		

Classifications

ETIM 6.0	EC000046	eClass 6.2	27-14-07-02
eClass 9.0	27-14-07-02	eClass 9.1	27-14-07-02

Approvals

ROHS	Conform
------	---------

Data sheet

Accessories
CB-DT 200/4.5 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

