

SAIE-M12S-4S-TL-HW-PG9**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIE-M12S-4S-TL-HW-PG9
Order No.	1467710000
Version	Built-in plugs, M12, No. of poles: 4
GTIN (EAN)	4050118273151
Qty.	10 pc(s).

SAIE-M12S-4S-TL-HW-PG9

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	19.25 g
------------	---------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

General data

Coding	A	Conductor O.D.	-
Connection thread	M12	Contact surface	Gold-plated
Housing main material	Zinc diecast	No. of poles	4
Protection degree	IP67, when fully mounted	Rated current	4 A
Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)	Rated voltage	250 V
Rated voltage (text)	250 V (4-pole)/ 60 V (5-pole)/ 30 V (8 and 12-pole)	Temperature range of housing	-20 ... +90 °C
Type of connection	Pin		

Classifications

ETIM 5.0	EC002635	ETIM 6.0	EC002638
eClass 6.2	27-26-07-02	eClass 7.1	27-44-01-02
eClass 8.1	27-44-01-02	eClass 9.0	27-44-03-09
eClass 9.1	27-44-03-09		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN FL FIELDWIRING EN
Engineering Data	STEP

SAIE-M12S-4S-TL-HW-PG9**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com**Drawings****Pole scheme**