
W-Series
WDU 70N/35 IR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image



Klippon® Connect with clamping yoke Technology
The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easer and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WDU 70N/35 IR
Order No.	1393420000
Version	Feed-through terminal, Screw connection, 70 mm², 1000 V, 192 A, dark beige
GTIN (EAN)	4050118495089
Qty.	10 pc(s).

W-Series
WDU 70N/35 IR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	20.5 mm	Width (inches)	0.807 inch
Height	75 mm	Height (inches)	2.953 inch
Depth	85 mm	Depth (inches)	3.346 inch
Depth including DIN rail	86 mm	Net weight	119.233 g

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

Rating data IECEx/ATEX

Certificate No. (ATEX)	DEMKO14ATEX1338U	Certificate No. (IECEX)	IECEXULD14.0005U
Max. voltage (ATEX)	690 V	Current (ATEX)	184 A
Wire cross section max. (ATEX)	70 mm²	Max. voltage (IECEX)	690 V
Current (IECEX)	184 A	Wire cross section max. (IECEX)	70 mm²
Marking EN 60079-7	Ex eb II C Gb	Ex 2014/34/EU label	II 2 G D

System specifications

Version	Screw connection, for screwable cross-connection, in closed state	Tightening torque (clamping screw for aluminium conductors)	12 Nm
Tightening torque (clamping screw for copper conductors)	8...12 Nm	End cover plate required	No
Number of potentials	1	Number of levels	1
No. of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35	N-function	No
PE function	No	PEN function	Yes

Additional technical data

Installation advice	Direct mounting	Number of similar terminals	1
Open sides	closed	Type of mounting	Snap-on

Weidmüller

W-Series
WDU 70N/35 IR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Conductors for clamping (rated connection)

Blade size	TX 40	Clamping range, max.	95 mm²
Clamping range, min.	16 mm²	Clamping screw	M 8
Connection cross-section, stranded, max.	95 mm²	Connection cross-section, stranded, min.	16 mm²
Connection direction	on side	Gauge to IEC 60947-1	B11
Number of connections	2	Stripping length	22 mm
Tightening torque, max.	12 Nm	Tightening torque, min.	8 Nm
Type of connection	Screw connection	Wire connection cross section AWG, max.	AWG 2/0
Wire connection cross section AWG, min.	AWG 6	Wire connection cross section, finely stranded, max.	70 mm²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	70 mm²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	16 mm²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	50 mm²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	16 mm²
Wire connection cross-section, finely stranded, min.	16 mm²	Wire connection cross-section, solid core, max.	16 mm²
Wire connection cross-section, solid core, min.	16 mm²		

Rating data

Rated cross-section	70 mm²	Rated voltage	1,000 V
Rated current	192 A	Current at maximum wires	232 A
Standards	IEC 60947-7-1	Volume resistance according to IEC 60947-7-x	0.17 mΩ
Rated impulse withstand voltage	8 kV	Pollution severity	3

UL rating data

Certificate No. (cURus)	E60693	Conductor size Factory wiring max. (cURus)	0 AWG
Conductor size Factory wiring min. (cURus)	6 AWG	Conductor size Field wiring max. (cURus)	0 AWG
Conductor size Field wiring min. (cURus)	6 AWG	Current size C (cURus)	150 A
Voltage size C (cURus)	600 V		

Classifications

ETIM 3.0	EC000897	ETIM 5.0	EC000897
ETIM 6.0	EC000897	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-20	eClass 6.2	27-14-11-20
eClass 7.1	27-14-11-20	eClass 8.1	27-14-11-20
eClass 9.0	27-14-11-20	eClass 9.1	27-14-11-20

Approvals

Approvals



W-Series
WDU 70N/35 IR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	IECEx Certificate ATEX Certificate
Engineering Data	STEP
User Documentation	NTI WDU/WPE 70N/35

Safety note

Safety notice	Safety Information

W-Series
WDU 70N/35 IR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings