

VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“For more than 35 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

SPS-DUO-PD USB CHARGING STATION

CE

VERSION 05/19

N° 1954695

This 7-port USB charging station is intended for mobile devices such as mobile phones, smartphones and tablet computers. It is powered by the included adaptor and has over-current protection.

FEATURES:

Dual Type-C™ PD USB charging station with 7 outputs // 5 USB-A outputs for charging USB devices // Rack for up to 7 mobile phones, smartphones or tablet computers //

TECHNICAL DATA:

Charging Station	
Input voltage / current	21 V/DC 3 A
Charging output	7 (2x USB Type-CTM PD, 5x USB Type-A)
Output	USB Type-CTM PD 18 W: 5 – 12 V/DC 1.5 – 3 A, max. 18 W USB Type-CTM PD 30 W: 5 – 20 V/DC 1.5 – 3 A, max. 30 W USB Type-A: 5x 5 V/DC 2.4 A, max. 48 W Combined output max. 63 W
Operating conditions	0 to 40 °C, 5 – 90 % relative humidity
Storage conditions	-10 to +55 °C, 5 – 90 % relative humidity
Power cord	1.2 m
Dimensions (L x W x H)	90 x 140 x 66.5 mm
Weight	328 g (with accessories)
Power Adaptor	
Operating voltage	100 - 240 V/AC, 50/60 Hz
Output	21 V/DC 3 A max. 63 W
Protection class	II

PACKAGE CONTENTS:

USB charging station // Power adaptor // Power cord (1.2 m) // Operating instructions //



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.
© Copyright 2019 by Conrad Electronic SE. 1954695_v1_0519_02_dh_ds(1)