


REV	DESCRIPTION OF CHANGE	DATE



FIBER SPECIFICATION

ITEM		SPEC
CENTER CORE	MATERIAL	PLASTIC FIBER
	CONSTRUCT	MM/NO. 0.98MM*1
	O. D.	MM 0.98
OUTER COATING	MATERIAL	PE
	O. D.	MM 2.2
	COLOR	BLACK
PVC JACKET	MATERIAL	PVC
	O. D.	MM 6.0 ± 0.1
	COLOR	BLACK

TECHNOLOGICAL PARAMETER

ITEM	SPEC
Fiber Diameter	1mm
Outside Diameter	2.2mm
Fiber Material	PMMA
Application Lighwave	650nm
Attenuation	< 0.18dB/m
Bend Radius	5Xcore Diameter
Used Temperature	-15° - 80°
Connection Loss	< 0.5dB
Outtter PVC Diameter	6.0 ± 0.1

Requirements:

1. Appearance shape plastic, strong plastic, such as noise, shrinkage defects
2. All materials must meet the RoHS standard

NO.	Length
1	500 ± 15
2	1000 ± 30
3	1500 ± 30
4	3000 ± 50
5	5000 ± 50

④	OUTER MOLDED	45P Black PVC		
③	SHELL	Color aluminum shell, Screen printing black, The other side a "DIGITAL", "DIGITAL" + arrow	2PCS	
②	CONN	Optical fiber plug Gold plated	2PCS	
①	CABLE	1/1.0 TOSLING*1C PE2.2+PVC OD:6.0MM 85P BLACK PVC		
NO.	SPECIFICATION STANDARD		QTY	REMARK

	SCALE	1:1	DWG NO	DESIGN	Aosion	CHECKED	APPROVED
	UNIT	mm	TW102A027	REV	A1	DATE	2014-01-10