

LogiLink®




4K Mini DisplayPort to HDMI Adapter

Art. No.: CV0036B

CV0036B is a new generation Mini DisplayPort™ to HDMI™ converter that receives both video and audio streams from an upstream Mini DisplayPort Source link and converts to a HDMI output.

Features:

- » Integrates a complete DisplayPort receiver and complete HDMI transmitter for video format conversion
- » Compliant with DisplayPort 1.2 input, video and audio
- » Compliant with HDMI high speed with Ethernet specification
- » Up to 300MHz color Rate for Stereoscopic 3D
- » Low power consumption (standby mode 25mW)
- » Maximum resolution 3840 x 2160@30Hz
- » Supports HDCP1.3 content protection
- » Supports multiple color format: RGB 6/8/10/12 bpc (bit per component), YCbCr 4:4:4, and YCbCr 4:2:2 8/10/12 bpc
- » Powered from Mini DisplayPort port source



Specification:

Input Connector	Mini DisplayPort Male 20pin
Output Connector	HDMI Female type A 19pin
Vertical Frequency Range	50/60Hz
Video Amplifier Bandwidth	Up to 5.4Gbps
Resolution	Max. resolution 3840 x 2160@30Hz Support 3D mode



Made in China



RoHS
compliant



* The specifications and pictures are subject to change without notice.
*All trade names referenced are the registered namework of their respective owners.

LogiLink®



4K Mini DisplayPort to HDMI Adapter

Art. No.: CV0036B

Operating Temperature	0°C - 70°C
Operating Humidity	10% to 85 % RH (no condensation)
Storage Temperature	-10 °C - 80 °C
Storage Humidity	5% to 90 % RH (no condensation)
Power Consumption (Max)	1W
Dimension	225 x 45 x 15mm
Weight	Approx. 30g
Cable Length	15cm



Package Contents:

- » 1 x Mini DisplayPort to HDMI Adapter
- » 1 x User Manual

Package Informations:

- » Packing Dimension: 235 x 75 x 25mm
- » Packing Weight: kg
- » Carton Dimension: 520 x 320 x 285mm
- » Carton Q'ty: 80pcs
- » Carton Weight: 7.1kg



* The specifications and pictures are subject to change without notice.
*All trade names referenced are the registered namework of their respective owners.

Made in China

Best Connectivity