





RoHS compliant



suitable for cable AWG 22

Capacitor value 1'000 pF

**MATERIALS**

- Insulator: Thermoplastic UL 94-V-0 black
- Contact: Machined / Copper alloy
- Contact finish: Quality class 2
- Shell: steel tin plated

**CHARAKTERISTICS**

- Working voltage: 100V
- Current rating: 7.5A
- Contact resistance: max. 10mΩ - DIN41652
- Insulation resistance: >1GΩ
- Temperature range: -55° to +125°C

General tolerances (Deltron standard)			
size in mm	> 0.5	> 3	> 30
	up to 3	up to 6	up to 120
tolerances	±0.1	±0.2	±0.3

modification	Rev.	Rev.	Rev.	DE002738 part no.		
	Rev.	Rev.	Rev.			
D15PZ/2FP102	1.5:1 scale	drawn	07.11.2007	mr		
		checked				
		approved				
		Industrie Neuhof 8c CH-3422 Kirchberg <a href="http://www.d-sub.swiss">www.d-sub.swiss</a>		K052005 drawing no.		