


## DV M TT 255 FM (951 315)


- Prewired spark-gap-based type 1 and type 2 combined lightning current and surge arrester consisting of a base part and plug-in protection modules
- Maximum system availability due to RADAX Flow follow current limitation, Capable of protecting terminal equipment



Figure without obligation



Basic circuit diagram DV M TT 255 FM



Dimension drawing DV M TT 255 FM

Modular combined lightning current and surge arrester for TT and TN-S systems (3+1 configuration).

| Type   | DV M TT 255 FM<br>951 315   |
|--|---|
| <b>Part No.</b>  |   |
| SPD according to EN 61643-11 / IEC 61643-11  | type 1 + type 2 / class I + class II                              |
| Energy coordination with terminal equipment ( $\leq 10$ m)   | type 1 + type 2 + type 3  |
| Nominal voltage (a.c.) ( $U_N$ )   | 230 / 400 V (50 / 60 Hz)  |
| Max. continuous operating voltage (a.c.) [L-N] ( $U_C$ )   | 264 V (50 / 60 Hz)  |
| Max. continuous operating voltage (a.c.) [N-PE] ( $U_{C(N-PE)}$ )  | 255 V (50 / 60 Hz)  |
| Lightning impulse current (10/350 $\mu$ s) [L1+L2+L3+N-PE] ( $I_{\text{total}}$ )  | 100 kA  |
| Specific energy [L1+L2+L3+N-PE] (W/R)  | 2.50 MJ/ohms  |
| Lightning impulse current (10/350 $\mu$ s) [L-N]/[N-PE] ( $I_{\text{imp}}$ )   | 25 / 100 kA   |
| Specific energy [L-N]/[N-PE] (W/R)   | 156.25 kJ/ohms / 2.50 MJ/ohms                                     |
| Nominal discharge current (8/20 $\mu$ s) [L-N]/[N-PE] ( $I_n$ )  | 25 / 100 kA   |
| Voltage protection level [L-N]/[N-PE] ( $U_P$ )  | $\leq 1.5 / \leq 1.5$ kV  |
| Follow current extinguishing capability [L-N]/[N-PE] ( $I_h$ )   | 50 kA <sub>rms</sub> / 100 A <sub>rms</sub>                       |
| Follow current limitation / Selectivity  | no tripping of a 20 A gG fuse up to 50 kA <sub>rms</sub> (prosp.) |
| Response time ( $t_s$ )  | $\leq 100$ ns   |
| Max. backup fuse (L) up to $I_k = 50$ kA <sub>rms</sub>  | 315 A gG  |
| Max. backup fuse (L-L')  | 125 A gG  |
| Temporary overvoltage (TOV) [L-N] ( $U_T$ ) – Characteristic   | 440 V / 120 min. – withstand                                      |
| Temporary overvoltage (TOV) [N-PE] ( $U_T$ ) – Characteristic  | 1200 V / 200 ms – withstand                                       |
| Operating temperature range [parallel] / [series] ( $T_u$ )  | -40 °C ... +80 °C / -40 °C ... +60 °C                             |
| Operating state / fault indication   | green / red   |
| Number of ports  | 1   |
| Cross-sectional area (L1, L1', L2, L2', L3, L3', N, N', PE, $\pm$ ) (min.)   | 10 mm <sup>2</sup> solid / flexible                               |
| Cross-sectional area (L1, L2, L3, N, PE) (max.)  | 50 mm <sup>2</sup> stranded / 35 mm <sup>2</sup> flexible         |
| Cross-sectional area (L1', L2', L3', N', $\pm$ ) (max.)  | 35 mm <sup>2</sup> stranded / 25 mm <sup>2</sup> flexible         |
| For mounting on  | 35 mm DIN rails acc. to EN 60715                                  |
| Enclosure material   | thermoplastic, red, UL 94 V-0                                     |
| Place of installation / Degree of protection   | indoors / IP 20   |
| Capacity   | 8 module(s), DIN 43880  |
| Approvals  | KEMA, VDE, UL   |
| Type of remote signalling contact  | changeover contact  |
| Switching capacity (a.c.)  | 250 V / 0.5 A   |
| Switching capacity (d.c.)  | 250 V / 0.1 A; 125 V / 0.2 A; 75 V / 0.5 A                        |
| Cross-sectional area for remote signalling terminals   | max. 1.5 mm <sup>2</sup> solid / flexible                         |
| Extended technical data:   | -----   |
| Voltage protection level [L-PE] ( $U_P$ )  | 2.2 kV  |
| For use in switchgear installations with prospective short-circuit currents of more than 50 kA <sub>rms</sub> (tested by the German VDE) | -----   |
| - Max. prospective short-circuit current   | 100 kA <sub>rms</sub> (220 kA <sub>peak</sub> )                   |
| - Limitation / Extinction of mains follow currents   | up to 100 kA <sub>rms</sub> (220 kA <sub>peak</sub> )             |
| - Max. backup fuse (L) up to $I_k = 100$ kA <sub>rms</sub>   | 315 A gG  |
| Weight   | 1,28 kg   |
| Customs tariff number (Comb. Nomenclature EU)  | 85363090  |
| GTIN   | 4013364108189   |
| PU   | 1 pc(s)   |

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.