


JZ-603-CY

Multi approval control cable, oil resistant, Cu-screened,
EMC-preferred, meter marking



Technical data

- Special PVC control cable with oil resistant outer sheath to DIN VDE 0285-525-2-51, DIN EN 50525-2-51 and to UL Style 2587
- **Temperature range**
HAR
flexing -5°C to +70°C
fixed installation -40°C to +70°C
UL/CSA
flexing -5°C to +90°C
fixed installation -40°C to +90°C
- **Nominal voltage**
HAR U₀/U 300/500 V
UL/CSA 600 V
- **Test voltage**
3000 V
- **Breakdown voltage**
min. 6000 V
- **Insulation resistance**
min. 20 MOhm x km
- **Minimum bending radius**
flexing 10x cable Ø
fixed installation 5x cable Ø
- **Radiation resistance**
up to 80x10⁶ cJ/kg (up to 80 Mrad)
- **Coupling resistance**
max. 250 Ohm/km

Cable structure

- Bare copper, fine wire conductor to DIN VDE 0295 cl.5, BS 6360 cl.5 and IEC 60228 cl.5
- Core insulation of special PVC compound type T12 to DIN VDE 0207-363-3 / DIN EN 50363-3 and class 43 acc. to UL Std.1581
- Core identification to DIN VDE 0293 black cores with continuous white numbering
- GN-YE conductor, 3 cores and above in the outer layer
- Cores stranded in layers with optimal lay length
- PVC based inner sheath
- Tinned copper braiding screening, 85% coverage
- Outer sheath of special PVC, oil resistant compound type TM5 to DIN VDE 0207-363-4-1/DIN EN 50363-4-1 and class 43 acc. to UL Std.1581
- Sheath colour: grey (RAL 7001)
- With meter marking

Properties

- The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers
- ### Tests
- PVC self-extinguishing and flame retardant acc. to DIN VDE 0482-332-1-2, DIN EN 60332-1-2, IEC 60332-1-2 (equivalent DIN VDE 0472 part 804 test method B), UL VW-1, CSA FT1
 - Oil resistant to DIN VDE 0473-811-404/ DIN EN 60811-404, UL 1581 part 50.182.

Note

- G = with GN-YE conductor
x = without GN-YE conductor (OZ)
- AWG sizes are approximate equivalent values. The actual cross section is in mm².
- Unscreened analogue type:

JZ-603

Application

UL-CSA-HAR approved cables offer any company exporting anywhere in the world, primarily designed for exporters, used in machine tools, control systems, assembly lines and other industrial equipment. These cables are suitable for flexible use for medium mechanical stresses with free movements in dry, moist and wet rooms but not for open air.

EMC = Electromagnetic compatibility

To optimize the EMC features we recommend a large round contact of the copper braiding on both ends.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

Part no.	No. cores x cross-sec. mm ²	AWG-No.	Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km
83709	2 x 0,5	20	8,0	41,0	90,0
83720	3 G 0,5	20	8,3	45,0	105,0
83721	4 G 0,5	20	8,9	54,0	123,0
83722	5 G 0,5	20	9,7	66,0	147,0
83723	7 G 0,5	20	11,2	79,0	195,0
83724	12 G 0,5	20	13,6	137,0	276,0
83725	18 G 0,5	20	15,4	156,0	418,0
83726	25 G 0,5	20	18,6	250,0	504,0
83727	34 G 0,5	20	20,8	316,0	632,0
83728	41 G 0,5	20	22,6	348,0	750,0
83729	50 G 0,5	20	24,8	407,0	968,0
83730	61 G 0,5	20	26,0	520,0	1068,0
83710	2 x 0,75	19	8,3	46,0	101,0
83731	3 G 0,75	19	8,6	57,0	127,0
83732	4 G 0,75	19	9,4	63,0	155,0
83733	5 G 0,75	19	10,1	76,0	180,0
83734	7 G 0,75	19	11,9	100,0	225,0
83735	12 G 0,75	19	14,2	175,0	326,0
83736	18 G 0,75	19	16,6	240,0	457,0
83737	25 G 0,75	19	20,0	306,0	635,0
83738	34 G 0,75	19	22,4	346,0	805,0
83739	41 G 0,75	19	24,0	403,0	908,0
83740	50 G 0,75	19	26,2	470,0	1155,0
83741	61 G 0,75	19	30,0	550,0	1400,0

Part no.	No. cores x cross-sec. mm ²	AWG-No.	Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km
83711	2 x 1	18	8,6	54,0	113,0
83742	3 G 1	18	9,2	64,0	144,0
83743	4 G 1	18	9,8	76,0	178,0
83744	5 G 1	18	10,7	89,0	205,0
83745	7 G 1	18	12,5	114,0	263,0
83746	12 G 1	18	15,1	186,0	424,0
83747	18 G 1	18	17,3	284,0	560,0
83748	25 G 1	18	21,1	387,0	760,0
83749	34 G 1	18	23,5	500,0	945,0
83750	41 G 1	18	25,5	578,0	1151,0
83751	50 G 1	18	27,6	681,0	1300,0
83752	61 G 1	18	32,4	710,0	1500,0
83712	2 x 1,5	16	9,6	64,0	144,0
83753	3 G 1,5	16	10,1	82,0	160,0
83754	4 G 1,5	16	11,0	99,0	210,0
83755	5 G 1,5	16	12,3	123,0	240,0
83756	7 G 1,5	16	14,2	148,0	305,0
83757	12 G 1,5	16	17,1	274,0	482,0
83758	18 G 1,5	16	20,0	386,0	611,0
83759	25 G 1,5	16	24,0	531,0	950,0
83760	34 G 1,5	16	27,1	671,0	1200,0
83761	41 G 1,5	16	29,7	840,0	1400,0
83762	50 G 1,5	16	31,8	997,0	1665,0
83763	61 G 1,5	16	34,6	1120,0	1852,0

Continuation ▶

JZ-603-CY

Multi approval control cable, oil resistant, Cu-screened,
EMC-preferred, meter marking



Part no.	No. cores x cross-sec. mm ²	AWG-No.	Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km
83713	2 x 2,5	14	11,4	110,0	189,0
83764	3 G 2,5	14	12,0	148,0	244,0
83765	4 G 2,5	14	13,4	169,0	296,0
83766	5 G 2,5	14	14,6	220,0	367,0
83767	7 G 2,5	14	17,2	284,0	478,0
83768	12 G 2,5	14	21,2	470,0	622,0

Part no.	No. cores x cross-sec. mm ²	AWG-No.	Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km
83769	18 G 2,5	14	24,8	572,0	1010,0
83770	25 G 2,5	14	29,8	740,0	1375,0
83771	34 G 2,5	14	33,4	1179,0	1893,0
83772	50 G 2,5	14	39,0	1660,0	2666,0
83773	61 G 2,5	14	41,0	1992,0	3077,0

Dimensions and specifications may be changed without prior notice. (RN01)