


DSH B TNS 255 FM (941 406)


- Application-optimised and prewired spark-gap-based type 1 and type 2 combined lightning current and surge arrester
- Compact design due to space-saving spark gap technology with a width of only 1 module / pole
- Meets the minimum requirements according to IEC 60364-5-53 concerning the nominal discharge capacity I_n and the lightning current discharge capacity I_{imp} in case of overhead line supply



Figure without obligation



Basic circuit diagram DSH B TNS 255 FM



Dimension drawing DSH B TNS 255 FM

Application-optimised and prewired combined lightning current and surge arrester for TN-S systems; with floating remote signalling contact.

Type	DSH B TNS 255 FM
Part No.	941 406
SPD according to EN 61643-11 / IEC 61643-11	type 1 + type 2 / class I + class II
Energy coordination with terminal equipment (≤ 10 m)	type 1 + type 2 + type 3
Nominal voltage (a.c.) (U_n)	230 / 400 V (50 / 60 Hz)
Max. continuous operating voltage (a.c.) (U_c)	255 (50 / 60 Hz)
Lightning impulse current (10/350 μ s) [$L_1+L_2+L_3+N-PE$] (I_{total})	30 kA
Lightning impulse current (10/350 μ s) [L , $N-PE$] (I_{imp})	7.5 kA
Nominal discharge current (8/20 μ s) [$L/N-PE$]/[$L_1+L_2+L_3+N-PE$] (I_n)	12.5 / 50 kA
Voltage protection level [$L-PE$]/[$N-PE$] (U_p)	$\leq 1.5 / \leq 1.5$ kV
Follow current extinguishing capability (a.c.) (I_h)	25 kA _{rms}
Follow current limitation / Selectivity	no tripping of a 32 A gG fuse up to 25 kA _{rms} (prosp.)
Response time (t_a)	≤ 100 ns
Max. mains-side overcurrent protection	160 A gG
Temporary overvoltage (TOV) [$L-N$] (U_t) – Characteristic	440 V / 120 min. – withstand
Operating temperature range (T_u)	-40 °C ... +80 °C
Operating state / fault indication	green / red
Number of ports	1
Cross-sectional area ($L_1, L_2, L_3, N, PE, \frac{1}{2}$) (min.)	1.5 mm ² solid / flexible
Cross-sectional area ($L_1, L_2, L_3, N, PE, \frac{1}{2}$) (max.)	35 mm ² stranded / 25 mm ² flexible
For mounting on	35 mm DIN rails acc. to EN 60715
Enclosure material	thermoplastic, red, UL 94 V-0
Place of installation	indoor installation
Degree of protection	IP 20
Capacity	4 module(s), DIN 43880
Approvals	VDE
Type of remote signalling contact	changeover contact
Switching capacity (a.c.)	250 V / 0.5 A
Switching capacity (d.c.)	250 V / 0.1 A; 125 V / 0.2 A; 75 V / 0.5 A
Cross-sectional area for remote signalling terminals	max. 1.5 mm ² solid / flexible
Weight	429 g
Customs tariff number (Comb. Nomenclature EU)	85363090
GTIN	4013364328082
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.