

Han 10A/15EMV-AK



Part number	09 20 010 5425
Specification	Han 10A/15EMV-AK
HARTING eCatalogue	https://b2b.harting.com/09200105425

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings
	for surface mounted housings
	for cable to cable housing
	Metal
	With fixing cord
Type	Low construction
	High construction

Version

Locking type	Single locking lever
Size	10 A
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Surface (hood/housing)	Powder-coated
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6b: Lead as an alloying element in aluminium containing up to 0,4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	60.12 g
Country of origin	Germany
Customs tariff number	85389099