

# JZ-603

Multi approval control cable, oil resistant, meter marking



HELUKABEL JZ-603 <VDE><HAR> H05VV5-F 4 G 0,5 QMM AWM STYLE 2587 20AWG 4C VW-1 LL113926 CSA AWM I/II A/B 90°C 600V FT1 300/500V



## Technical data

- Special PVC control cable with oil resistant outer sheath to DIN VDE 0285-525-2-51/ DIN EN 50525-2-51 and UL Style 2587
- **Temperature range**  
HAR  
flexing -5°C to +70°C  
fixed installation -40°C to +70°C  
UL/CSA  
flexing -5°C to +90°C  
fixed installation -40°C to +90°C
- **Nominal voltage**  
HAR U<sub>0</sub>/U 300/500 V  
UL/CSA 600 V
- **Test voltage**  
3000 V
- **Breakdown voltage**  
min. 6000 V
- **Insulation resistance**  
min. 20 MOhm x km
- **Minimum bending radius**  
flexing 7,5x cable Ø  
fixed installation 4x cable Ø
- **Radiation resistance**  
up to 80x10<sup>6</sup> cJ/kg (up to 80 Mrad)

## Cable structure

- Bare copper conductor, to DIN VDE 0295 cl.5, fine wire, BS 6360 cl.5, IEC 60228 cl.5
- Core insulation of special PVC compound type T12 to DIN VDE 0207-363-3 / DIN EN 50363-3 and class 43 acc. to UL Std.1581
- Core identification to DIN VDE 0293 black cores with continuous white numbering
- GN-YE conductor, 3 cores and above in the outer layer
- Cores stranded in layers with optimal lay length
- Outer sheath of oil resistant special PVC compound type TM5 to DIN VDE 0207-363-4-1/DIN EN 50363-4-1 and class 43 acc. to UL Std.1581
- Sheath colour: grey (RAL 7001)
- With meter marking

## Properties

- The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers

## Tests

- PVC self-extinguishing and flame retardant acc. to DIN VDE 0482-332-1-2, DIN EN 60332-1-2, IEC 60332-1-2 (equivalent DIN VDE 0472 part 804 test method B), UL VW-1, CSA FT1
- Oil resistant to DIN VDE 0473-811-404/ DIN EN 60811-404, UL-Std.1581 part 50.182

## Note

- G = with GN-YE conductor  
x = without GN-YE conductor (OZ)
- AWG sizes are approximate equivalent values. The actual cross section is in mm<sup>2</sup>.
- Screened analogue type:  
**JZ-603-CY**

## Application

UL-CSA-HAR approved cables offer any company exporting anywhere in the world, primarily designed for exporters, used in machine tools, control systems, assembly lines and other industrial equipment. These cables are suitable for flexible use for mechanical stresses with free movements in dry, moist and wet rooms but not for open air.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

Part no.	No.cores x cross-sec. mm <sup>2</sup>	AWG-No.	Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km
83704	2 x 0,5	20	5,8	9,6	52,0
83650	3 G 0,5	20	6,1	14,0	63,0
83651	4 G 0,5	20	6,7	19,0	69,0
83652	5 G 0,5	20	7,3	24,0	87,0
83653	7 G 0,5	20	8,8	34,0	119,0
83654	12 G 0,5	20	11,1	58,0	198,0
83655	18 G 0,5	20	12,9	86,0	266,0
83656	25 G 0,5	20	16,0	120,0	380,0
83657	34 G 0,5	20	17,7	163,0	508,0
83658	41 G 0,5	20	19,5	197,0	594,0
83659	50 G 0,5	20	21,3	240,0	715,0
83660	61 G 0,5	20	23,8	293,0	840,0
83705	2 x 0,75	19	6,1	14,4	66,0
83661	3 G 0,75	19	6,5	22,0	76,0
83662	4 G 0,75	19	7,1	29,0	85,0
83663	5 G 0,75	19	7,9	36,0	113,0
83664	7 G 0,75	19	9,5	50,0	144,0
83665	12 G 0,75	19	11,6	86,0	245,0
83666	18 G 0,75	19	13,9	130,0	327,0
83667	25 G 0,75	19	17,1	180,0	466,0
83668	34 G 0,75	19	19,1	245,0	626,0
83669	41 G 0,75	19	20,9	296,0	747,0
83670	50 G 0,75	19	23,0	360,0	896,0
83671	61 G 0,75	19	25,3	439,0	1070,0
83706	2 x 1	18	6,4	19,2	70,0
83672	3 G 1	18	6,8	29,0	88,0
83673	4 G 1	18	7,5	39,0	99,0
83674	5 G 1	18	8,4	48,0	132,0
83675	7 G 1	18	10,0	67,0	170,0
83676	12 G 1	18	12,5	115,0	285,0

Part no.	No.cores x cross-sec. mm <sup>2</sup>	AWG-No.	Outer Ø app. mm	Cop. weight kg / km	Weight app. kg / km
83677	18 G 1	18	14,7	173,0	405,0
83678	25 G 1	18	18,0	240,0	570,0
83679	34 G 1	18	20,3	326,0	742,0
83680	41 G 1	18	22,4	394,0	885,0
83681	50 G 1	18	24,3	480,0	1071,0
83682	61 G 1	18	26,8	586,0	1265,0
83707	2 x 1,5	16	7,4	28,8	91,0
83683	3 G 1,5	16	8,0	43,0	110,0
83684	4 G 1,5	16	8,7	58,0	141,0
83685	5 G 1,5	16	9,8	72,0	167,0
83686	7 G 1,5	16	11,9	101,0	225,0
83687	12 G 1,5	16	14,5	173,0	361,0
83688	18 G 1,5	16	17,4	259,0	518,0
83689	25 G 1,5	16	21,3	360,0	730,0
83690	34 G 1,5	16	24,1	490,0	945,0
83691	41 G 1,5	16	26,2	591,0	1135,0
83692	50 G 1,5	16	28,8	720,0	1381,0
83693	61 G 1,5	16	31,5	878,0	1640,0
83708	2 x 2,5	14	9,1	48,0	125,0
83694	3 G 2,5	14	9,9	72,0	169,0
83695	4 G 2,5	14	11,0	96,0	209,0
83696	5 G 2,5	14	12,0	120,0	256,0
83697	7 G 2,5	14	14,6	168,0	340,0
83698	12 G 2,5	14	18,1	288,0	579,0
83699	18 G 2,5	14	22,1	432,0	851,0
83700	25 G 2,5	14	26,5	600,0	1175,0
83701	34 G 2,5	14	29,9	816,0	1529,0
83702	50 G 2,5	14	35,2	1200,0	2290,0
83703	61 G 2,5	14	38,4	1464,0	2724,0

Dimensions and specifications may be changed without prior notice. (RN01)