


Han ES AV Pos. 6 Insert Term. Block righ



Part number	09 33 006 4739
Specification	Han ES AV Pos. 6 Insert Term. Block righ
HARTING eCatalogue	https://b2b.harting.com/09330064739

Identification

Category	Inserts
Series	Han [®] ES AV
Element	Terminal block connector
Specification	Right hand version Single contour (SK)

Version

Termination method	Cage-clamp termination
Gender	Female
Size	6 B
Number of contacts	6
PE contact	Yes

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Electrical data acc. to IEC 61984	16 A 500 V 6 kV 3
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated current acc. to UL	12 A
Rated voltage acc. to UL	600 V
Rated current acc. to CSA	12 A
Insulation resistance	≥10 ¹⁰ Ω
Contact resistance	≤4 mΩ
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	1
Net weight	77 g
Country of origin	Germany
Customs tariff number	85366990