

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

"Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success."

CAA-1L 16 MEASURING ADAPTER



VERSION 12/21

N° 1973631

The measuring adapter measures together with a clamp meter or multimeter the electrical current and voltage of single-phase devices with corresponding connectors. The measuring adapter is inserted between the electrical consumer and the socket. The measuring adapter may only be used in the range of the overvoltage category CAT II in AC voltage networks with a nominal voltage of max. 250 V/AC which are fused with 16 A.

FEATURES:

- Easy current measurement in closed line systems with power plugs //
- Facilitates measuring of current and leakage current at the same time //
- Overvoltage category CAT II //

PACKAGE CONTENTS:

Adapter // Operating instructions

TECHNICAL DATA:

Connection plug/socket	IEC C19/C20
Nominal voltage	max. 250 V/AC, 50/60 Hz
Nominal current	max. 16 A
Protection type	IP40
Conductor cross section	3 x 1,5 mm ²
Operating conditions	0 to +53 °C, 0 – 75 % RH (non-condensing)
Storage conditions	0 to +53 °C, 0 – 75 % RH (non-condensing)
Overvoltage category	CAT II 250 V/AC, 50/60 Hz, 16 A
Bar diameter of the measuring chambers	approx. 13 mm
Measuring sockets	4 mm
Dimensions (L x W x H)	approx. 1797 x 90 x 45 mm
Weight	approx. 410 g

