

Han Brid-Sti-c Abschlußstecker Met. M20



Part number	09 12 006 2692
Specification	Han Brid-Sti-c Abschlußstecker Met. M20
HARTING eCatalogue	https://b2b.harting.com/09120062692

Identification

Category	Inserts
Series	Han-Brid®
Identification	Han-Brid® Cu
Specification	Bus terminator

Version

Gender	Male
Size	3 A
Number of contacts	2
Additional contacts	+ 4 electrical contacts 10 A + option for PE

Technical characteristics

Electrical data acc. to IEC 61984	10 A 50 V 0.8 kV 3
Rated current	10 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	$\geq 10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material (hood/housing)	Zinc die-cast
Colour (hood/housing)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption



Pushing Performance

Material properties

RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	88.8 g
Country of origin	Germany
Customs tariff number	85366990