

Han K4/4-M 6-16mm²



Part number	09 38 008 2611
Specification	Han K4/4-M 6-16mm ²
HARTING eCatalogue	https://b2b.harting.com/09380082611

Identification

Category	Inserts
Series	Han-Com [®]
Identification	Han [®] K 4/4

Version

Termination method	Axial screw termination / cage-clamp termination
Gender	Male
Size	10 B
Number of contacts	4
Additional contacts	+ 4 additional signal contacts
PE contact	Yes
Details	Not finger safe

Technical characteristics

Conductor cross-section	6 ... 16 mm ² 0.14 ... 2.5 mm ² Signal
Wire outer diameter	≤8.9 mm
Electrical data acc. to IEC 61984	63 A 690 V 8 kV 3
Rated current	63 A
Rated voltage	690 V
Rated impulse voltage	8 kV
Pollution degree	3
Electrical data, signal	16 A 250 V 4 kV 3
Rated current (signal)	16 A
Rated voltage (signal)	250 V
Rated impulse voltage (signal)	4 kV
Pollution degree (signal)	3
Rated current acc. to UL	63 A
Rated voltage acc. to UL	600 V



Pushing Performance

Technical characteristics

Rated current acc. to UL (signal)	16 A
Rated voltage acc. to UL (signal)	230 V
Rated current acc. to CSA	63 A
Rated voltage acc. to CSA	600 V
Rated current acc. to CSA (signal)	16 A
Rated voltage acc. to CSA (signal)	230 V
Insulation resistance	$\geq 10^{10} \Omega$
Contact resistance	$\leq 0.5 \text{ m}\Omega$
Contact resistance, signal area	$\leq 3 \text{ m}\Omega$
Limiting temperature	-40 ... +125 °C
Stripping length	11 ... 12 mm 7 ... 9 mm Signal
Tightening torque	2 Nm @ 6 mm ² 3 Nm @ 10 mm ² 4 Nm @ 16 mm ²
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight 6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1
----------------	------------



Pushing Performance

Specifications and approvals

	IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	122.4 g
Country of origin	Germany
Customs tariff number	85366990