

# Han K 6/12 POS. M INSERT



Part number	09 38 018 2601
Specification	Han K 6/12 POS. M INSERT
HARTING eCatalogue	https://b2b.harting.com/09380182601

#### Identification

Category	Inserts
Series	Han-Com <sup>®</sup>
Identification	Han <sup>®</sup> K 6/12

### Version

Termination method	Axial screw termination / screw termination
Gender	Male
Size	16 B
Number of contacts	6
Additional contacts	+ 12 additional signal contacts
PE contact	Yes

#### Technical characteristics

recillical characteristics	
Conductor cross-section	2.5 8 mm² 0.2 2.5 mm² Signal
Wire outer diameter	≤6.1 mm
Electrical data acc. to IEC 61984	40 A 690 V 8 kV 3
Rated current	40 A
Rated voltage	690 V
Rated impulse voltage	8 kV
Pollution degree	3
Electrical data, signal	10 A 230/400 V 4 kV 3
Rated current (signal)	10 A
Rated voltage conductor-earth (signal)	230 V
Rated voltage conductor-conductor (signal)	400 V
Rated impulse voltage (signal)	4 kV
Pollution degree (signal)	3
Rated current acc. to UL	40 A
Rated voltage acc. to UL	600 V



### Technical characteristics

Rated current acc. to UL (signal)	10 A
Rated voltage acc. to UL (signal)	600 V
Rated current acc. to CSA	40 A
Rated voltage acc. to CSA	300 V
Rated current acc. to CSA (signal)	10 A
Rated voltage acc. to CSA (signal)	300 V
Insulation resistance	≥10 <sup>10</sup> Ω
Contact resistance	≤0.5 mΩ
Contact resistance, signal area	≤3 mΩ
Limiting temperature	-40 +125 °C
Stripping length	5 6 mm @ 2.5 mm <sup>2</sup> 5 6 mm @ 4 mm <sup>2</sup> 8 9 mm @ 6 mm <sup>2</sup> 7.5 mm Signal
Tightening torque	1.5 Nm @ 2.5 mm <sup>2</sup> 1.5 Nm @ 4 mm <sup>2</sup> 2 Nm @ 6 mm <sup>2</sup> 0.5 Nm Signal
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead



## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	147.1 g
Country of origin	Germany
Customs tariff number	85366990