




Pushing Performance

Han Q8/0-F-QL 1,5mm² fine strand wire



Part number	09 12 008 2734
Specification	Han Q8/0-F-QL 1,5mm ² fine strand wire
HARTING eCatalogue	https://b2b.harting.com/09120082734

Identification

Category	Inserts
Series	Han [®] Q
Identification	8/0

Version

Termination method	Han-Quick Lock [®] termination
Gender	Female
Size	Han-Compact [®]
Number of contacts	8
PE contact	Yes
Details	Black slide

Technical characteristics

Conductor cross-section	0.25 ... 1.5 mm ²
Electrical data acc. to IEC 61984	16 A 500 V 6 kV 3
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	≥10 ¹⁰ Ω
Contact resistance	≤3 mΩ
Limiting temperature	-40 ... +125 °C
Stripping length	10 mm
Mating cycles	≥500



Pushing Performance

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	31.92 g
Country of origin	Germany
Customs tariff number	85366990