

Han 16A-BU-C (17-32)



| | |
|--------------------|---|
| Part number | 09 20 016 3111 |
| Specification | Han 16A-BU-C (17-32) |
| HARTING eCatalogue | https://b2b.harting.com/09200163111 |

Identification

| | |
|---------------|--------------------|
| Category | Inserts |
| Series | Han A® |
| Specification | Continuing marking |

Version

| | |
|------------------------|--|
| Termination method | Crimp termination |
| Gender | Female |
| Size | 32 A |
| Number of contacts | 32 |
| PE contact | Yes |
| Contact identification | 17 ... 32 |
| Details | Please order crimp contacts separately. You need two inserts for a complete assembly! |

Technical characteristics

| | |
|-----------------------------------|----------------------------|
| Conductor cross-section | 0.14 ... 4 mm ² |
| Electrical data acc. to IEC 61984 | 16 A 250 V 4 kV 3 |
| Rated current | 16 A |
| Rated voltage | 250 V |
| Rated impulse voltage | 4 kV |
| Pollution degree | 3 |
| Rated voltage acc. to UL | 600 V |
| Insulation resistance | ≥10 ¹⁰ Ω |
| Limiting temperature | -40 ... +125 °C |
| Mating cycles | ≥500 |

Material properties

| | |
|-------------------|------------------------|
| Material (insert) | Polycarbonate |
| Colour (insert) | RAL 7032 (pebble grey) |



Pushing Performance

Material properties

| | |
|---|-----------|
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| | |
|----------------|---|
| Specifications | EN 60664-1 IEC 61984 |
| Approvals | DNV GL |
| UL / CSA | UL 1977 ECBT2.E235076 UL 2237 PVVA2.E318390 CSA-C22.2 No. 182.3 PVVA8.E318390 |

Commercial data

| | |
|-----------------------|----------|
| Packaging size | 1 |
| Net weight | 40.2 g |
| Country of origin | Germany |
| Customs tariff number | 85389099 |