

# Han EE 10 Pos. Insert Female Crimp



Part number	09 32 010 3101
Specification	Han EE 10 Pos. Insert Female Crimp
HARTING eCatalogue	https://b2b.harting.com/09320103101
Identification	
Category	Inserts
Series	Han <sup>®</sup> EE

#### Version

Termination method	Crimp termination
Gender	Female
Size	6 B
Number of contacts	10
PE contact	Yes
Details	Please order crimp contacts separately.

### **Technical characteristics**

Conductor cross-section	0.14 4 mm²
Conductor cross-section	AWG 26 AWG 12
Electrical data acc. to IEC 61984	16 A 500 V 6 kV 3
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	≥10 <sup>10</sup> Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500
Material properties	

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)

Page 1 / 2 | Creation date 2018-09-04 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



#### Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

#### Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 UL 2237 PVVA2.E318390 CSA-C22.2 No. 182.3 PVVA8.E318390

## Commercial data

Packaging size	1
Net weight	46 g
Country of origin	Romania
Customs tariff number	85366990